

## Ronde ponsen en matrijzen APS



Referentie	Referentie	ø in mm	APS 70	APS120
23-01-07	23-02-07	7	•	•
23-01-08	23-02-08	8	•	•
23-01-09	23-02-09	9	•	•
23-01-10	23-02-10	10	•	•
23-01-11	23-02-11	11	•	•
23-01-12	23-02-12	12	•	•
23-01-13	23-02-13	13	•	•
23-01-14	23-02-14	14	•	•
23-01-15	23-02-15	15	•	•
23-01-16	23-02-16	16	•	•
23-01-17	23-02-17	17	•	•
23-01-18	23-02-18	18	•	•
23-01-19	23-02-19	19	•	•
23-01-20	23-02-20	20	•	•
23-01-21	23-02-21	21	•	•
23-01-22	23-02-22	22	•	•
23-01-23	23-02-23	23		•
23-01-24	23-02-24	24		•
23-01-25	23-02-25	25*		•

\* Gebruik met borgmoer 23004-056 B

### Maximale materiaaldikte :

- Met materiaal volgens DIN S233: **0,8 × Ø gat**
- Met materiaal volgens DIN S275: **0,5 × Ø gat**

Deze ponsen en matrijzen zijn **compatibel met Nitto/Selfer ponsystemen**.

**Let op:** Bij sterk geoxideerd materiaal de pons smeren en regelmatig reinigen.