


# Repair Parts/ Pièces de Rechange









Item No./ Article	Part No./ N° de Pièce	Description
1	063259A	Metal Cover & Hex Screw (#8-32 x 3/16")
2	063260A	Solar Module & Screws (#6-32 x 5/16")
3	060334A	Battery Holder
4a	063261A	Urinal Sensor & Screws (#6-32 x 5/16")
4b	061384A	Water Closet Sensor & Screws (#6-32 x 5/16")
4c	061385A	Dual Flush Water Closet Sensor & Screws (#6-32 x 5/16")
5	060078A *	Screws for Cast Cap (4/pkg)
6	063262A	Mounting Flange
7	061024A	Regulating Screw & O-Ring
8	061353A	Cap/Solenoid & Regulating Screw Assembly for 0.5 Lpf (0.125 gpf) fixed urinals (see Table 1)
	061374A	Cap/Solenoid & Regulating Screw Assembly for 1.9 Lpf (0.5 gpf) fixed urinals (see Table 1)
	061356A	Cap/Solenoid & Regulating Screw Assembly for 1.9 Lpf (0.5 gpf) adjustable urinals (see Table 1)
	061354A	Cap/Solenoid & Regulating Screw Assembly for 4.2 Lpf (1.1 gpf) fixed water closets (see Table 1)
	061355A	Cap/Solenoid & Regulating Screw Assembly for 4.8 Lpf (1.27 gpf) fixed water closets (see Table 1)
	061325A	Cap/Solenoid & Regulating Screw Assembly for 6.0 Lpf (1.6 gpf) adjustable water closets & 6.0 Lpf (1.6 gpf) Dual Flush water closets (see Table 1)
9a	060507A *	Poppet Pin Pack (3/pkg) (see Table 1)
9b	060508A *	Poppet Pin Pack (3/pkg) (0.5 Lpf Valves only) (see Table 1)
9c	062025A *	Washer (3/pkg) (4.2 & 4.8 Lpf Valves only) (see Table 1)
10a	061323A	Diaphragm/Guide Assembly Complete - W/C (see Table 1)
10b	061324A	Diaphragm Guide Assembly for Urinals (See Table 1)
10c	060079A-MMO	Diaphragm only (12/pkg)
11	062007A	Brass Seat with O-Ring
12	061322A	Push Button, Cage, Cap Nut
13	060506A	Standard Adjustable Tail
14	060735A	Union Nut
15	060692A	Retaining Ring
16	060082A *	Adjustable Tail O-Ring Package (20/pkg)
17	060344A *	Filter Screen Kit (12/pkg)
18	060843A	Retrofit Check Stem Unit, Capnut & Button Complete
19	060844A	Seat Washer, Spring, Button & O-Ring Kit
20	060859A	Angle Stop with Union Nut & Tail Complete
21	060081A *	Plug Button Package (12/pkg)
22	060697A	1" Copper Sweat Inlet Adaptor
	060694A	¾" Copper Sweat Inlet Adaptor
	060764A	¾" FIP Inlet Adaptor
23	060504A	S/S Wall Flange & Cover Tube
24	060785A	Vacuum breaker sleeve complete
25	060782A	1½" x 10" (38 mm x 254 mm) V.B., coupling ring and tube complete
26	060094A	Coupling Ring
27	060004A	1½" Spud Flange
28	060778A	1½" Rough Coupling Nut & Washers
29	060083A *	1½" Slip Joint Washers (12/pkg)
30	060784A	¾" x 11½" VB, Ring & Tube Complete (Urinal)
31	060463A	¾" Coupling Nut, ¾" Washers & ¾" Spud Flange
32	060049A *	¾" (19mm) Rubber and fiber washers (12/pkg)

**NOTICE** \* Package quantities may change. Check the parts section of the latest Delta Commercial Faucet Price List for current quantities.

**AVIS** \* Les quantités dans les paquets peuvent varier. Vérifiez la section des pièces du plus récent catalogue de prix des produits commerciaux de Delta pour les quantités exactes.

**Table 1 - Cap/Pin/Diaphragm Configuration Table**  
**Tableau 1 - Table de Configuration du Capuchon/Tige/Diaphragme**

	Urinal/Urinoir			Water Closet/ Toilette		
	*Fixed/ *Non Réglable		Adjustable/ Ajustable	*Fixed/ *Non Réglable		Adjustable/ Ajustable & Dual Flush/ Chasse d'eau double
	**0.5 Lpf (0.125 gpf)	**1.9 Lpf (0.5 gpf)	1.9 Lpf (0.5 gpf)	**4.2 Lpf (1.1 gpf)	**4.8 Lpf (1.27 gpf)	6.0 Lpf (1.6 gpf)
<b>Cap/Solenoid &amp; Regulating Screw Assembly</b> (includes Cap, Solenoid, Regulating Screw)  <b>Ensemble Capuchon, Solénoïde et Vis de Réglage</b> (inclus capuchon, solénoïde et vis de réglage)	061353A 	061374A 	061356A 	061354A 	061355A 	061325A 
<b>Poppet Pin</b> <b>Tige Clapet</b>	060508A 	060507A 		060507A & 062025A 		
<b>Diaphragm Assembly</b> <b>Ensemble Guid/Diaphragme</b>	061324A 			061323A 		

**NOTICE** Must use all noted components listed in Table 1 to ensure correct flush volumes.

\* Fixed models have epoxy in the adjustment screw.

\*\* WaterSense® compliant when paired with a WaterSense fixture rated for the same flush volume.

**AVIS** Utiliser toutes les composantes identifiées au tableau 1 pour obtenir un volume de chasse approprié.

\* La vis de réglage des modèles non-réglable est immobilisée par une résine époxy.

\*\* Conforme à la norme WaterSense lorsque combiné à un appareil sanitaire approuvé WaterSense pour le même volume de chasse.