

SHOWA | 874R

SUPERIOR RESISTANCE TO HIGHLY CORROSIVE ACIDS AND CHEMICALS

Rough textured version of the SHOWA 874. The Ideal for those working with biohazards and specifically when handling ketones, amines and esters. Butyl rubber provides the highest permeation resistance to toxic gases and water vapours.

FEATURES

- › Impermeable for working in damp or greasy environments
- › Protection against ketones, alcohols, nerve agents
- › Provides the highest permeation resistance to gases and water vapors of any protective material used to make gloves
- › Unlined to reduce risk of lint contamination
- › Rough textured surface enhances grip
- › Length: 35cm
- › Thickness: 0.35mm
- › Rolled cuff



SUITABLE FOR

Typical Industries

- Agriculture
- Chemical
- Metal
- Municipal Services
- Petrochemical
- Army

Suitable Applications

- Chemical Handling
- Handling Oily Components
- Wet Work

CERTIFICATION

CAT III	EN 388:2016	EN ISO 374-1:2016/Type B	EN ISO 374-5:2016
0299	0010X	BIK	

See overleaf for explanation



874R

PRODUCT INFORMATION

MATERIALS	LINER:	Unsupported, unlined
	COATING:	Butyl
COLOUR	Black	
LENGTH (mm)	350 (size dependent)	
CUFF STYLE	Gauntlet	

ORDERING DETAILS

SIZE	CODE	PACKAGING
7/S	BST874R1	12 pairs per bag 12 pairs per case
8/M	BST874R2	
9/L	BST874R3	
10/XL	BST874R4	
11/XXL	BST874R5	


RECOMMENDATIONS FOR USE

- **USE:** Chemical resistant glove. Not suitable for thermal, electrical protection. Do not use near moving machines if there is a risk of entanglement
- **STORAGE:** Store in dry conditions in the original packaging and away from direct sunlight
- **CLEANING:** To clean, wipe with a damp cloth. Note: The performance characteristics of worn and laundered gloves may differ from the results shown. Inspect the gloves to ensure no damage is present
- **LIFETIME:** Service life depends on the glove application and therefore cannot be specified. It is the responsibility of user to ensure the glove is suitable for its intended use

CERTIFICATION LEGENDS



MECHANICAL HAZARDS EN 388:2016 PERFORMANCE LEVELS*



*If tests are not performed or are not applicable, 'X' will be placed instead of a number/letter



PROTECTION AGAINST MICRO-ORGANISMS EN 374-5

VIRUS = Glove has passed ISO 16604:2004 (method B)



RESISTANCE TO CHEMICAL PERMEATION - EN ISO 374:2016

CODE	CHEMICAL	CODE	CHEMICAL	TYPE OF GLOVES	BREAKTHROUGH TIME
A	Methanol	J	n-Heptane	A	≥30 min for at least 6 chemicals
B	Acetone	K	Sodium hydroxide 40%		
C	Acetonitrile	L	Sulphuric acid 96%	B	≥30 min for at least 3 chemicals
D	Dichloromethane	M	65% Nitric acid		
E	Carbon Disulfide	N	99% Acetic acid	C	≥10 min for at least 1 chemical
F	Toluene	O	25% Ammonium hydroxide		
G	Diethylamine	P	30% Hydrogen peroxide		
H	Tetrahydrofuran	S	40% Hydrofluoric acid		
I	Ethyl acetate	T	37% Formaldehyde		

EUROPE

www.globusgroup.com

E: sales@globus.co.uk
T: +44 (0)161 877 4747
F: +44 (0)161 877 4746

MIDDLE EAST AND AFRICA

www.globusgroup.com/gcc

E: gcc@globusgroup.com
T: +971 4 882 9962
F: +971 4 882 9963



Globus Group, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM
 Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES

©2020 Globus (Shetland) Ltd | SHO-DATA-874R_0620_1