

ш**н.** В0700R

UNSUPPORTED WITH A PVC COATING AND EXTENDED CUFF

A thin, lightweight glove with a second skin feel, which is ideal for industries where cleanliness is a priority. The flexible PVC coating provides chemical resistance and good grip.

FEATURES

- > Ultra-thin, light glove with a second skin feel
- Seals and protects the hand against chemicals whileremaining flexible
- Impermeable for working in damp or greasyenvironments
- > Lint-free, dust-free
- Fully coated with a scalloped edge and embossed finish
- ➤ Non-powdered, 'slip-on' treatment
- > Seamless liner prevents irritation
- > Surface enables a secure grip on slippery objects
- > Designed for easy movement and continuous wear
- > Extended protection on the forearm
- > Ergonomic Fit
- > Thickness: 0.3mm







SUITABLE FOR

Typical Industries

- Agriculture
- Electronics
- Healthcare
- Petrochemical
- Pharmaceutical

Suitable Applications

- Cleaning
- General Purpose
- Handling Pesticides
- Laboratories

CAT III EN 388:2016 EN ISO 3741:2016/Type C 0598 2000X K

See overleaf for explanation





B0700R

PRODUCT INFORMATION

MATERIALS	LINER:	Unsupported, unlined
	COATING:	PVC
COLOUR	White	
LENGTH (mm)	300	
CUFF STYLE	Gauntlet	

ORDERING DETAILS

SIZE	CODE	PACKAGING
7/S 8/M 9/L 10/XL	SHO7001 SHO7002 SHO7003 SHO7004	10 pairs per bag 240 pairs per case

RECOMMENDATIONS FOR USE

- USE: Light chemical resistant glove. Not suitable for thermal, electrical, cut and high chemicals handling. Do not use near moving machines if there is a risk of entanglement
- STORAGE: Store in dry conditions in the original packaging and away from direct sunlight
- CLEANING: To clean, wipe with a damp cloth. Note: The performance characteristics of worn and laundered gloves may differ from the results shown. Inspect the gloves to ensure no damage is present
- LIFETIME: Service life depends on the glove application and therefore cannot be specified. It is the responsibility of user to ensure the glove is suitable for its intended use

PROTECTION AGAINST


MICRO-ORGANISMS EN 374-5 VIRUS = Glove has passed ISO 16604: 2004 (method B)

8

CERTIFICATION LEGENDS



MECHANICAL HAZARDS EN 388:2016 PERFORMANCE LEVELS*



*If tests are not performed or are not applicable, 'X' will be placed instead of a number/letter



EUROPE

www.globusgroup.com

E: sales@globus.co.uk

+44 (0)161 877 4747

+44 (0)161 877 4746

RESISTANCE TO CHEMICAL PERMEATION - EN ISO 374:2016

CODE	CHEMICAL	CODE	CHEMICAL
A	Methanol	J	n-Heptane
В	Acetone	K	Sodium hydroxide 40%
C	Acetonitrile	L	Sulphuric acid 96%
D	Dichloromethane	M	65% Nitric acid
E	Carbon Disulfide	N	99% Acetic acid
F	Toluene	0	25% Ammonium hydroxide
G	Diethylamine	Р	30% Hydrogen peroxide
Н	Tetrahydrofurane	S	40% Hydrofluoric acid
1	Ethyl acetate	T	37% Formaldehyde

TYPE OF GLOVES	BREAKTHROUGH TIME
Α	≥30 min for at least 6 chemicals
В	≥30 min for at least 3 chemicals
С	≥10 min for at least 1 chemical

Globus[®] GROUP

MIDDLE EAST AND AFRICA

www.globusgroup.com/gcc

E: gcc@globusgroup.com T: +971 4 882 9962 F: +971 4 882 9963

Globus Group, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES

©2020 Globus (Shetland) Ltd | SHO-DATA-B0700R_0620_1