

BLACK, SINGLE-USE GLOVE WITH GRIP PATTERN, 100% NITRILE, POWDER-FREE, 240MM LONG

High performance, powder-free, black, nitrile single-use glove with patented TRXON grip pattern technology. Provides outstanding grip performances and chemical protection.

FEATURES

- › High-quality nitrile, soft and durable
- › Palm thickness 0.18mm (7mil), weight: 7.5g, size M
- › High resistance to penetration and projections of many chemicals
- › Patented TRXON grip pattern technology on both sides, offering outstanding grip properties in all conditions
- › Powder-free, latex-free, non-sterile, AQL 1.5
- › Chlorinated inside to offer increased comfort and reduce friction when donning
- › Anti-static properties due to inherent anti-static properties of nitrile
- › Lasts up to 5 times longer than regular single-use gloves in industrial applications
- › Ambidextrous for easy and quick donning



SUITABLE FOR


Typical Industries

- Aerospace
- Chemical
- Electronics
- Automotive
- Manufacturing
- Oil and Gas

Suitable Applications

- Chemical Handling
- Handling Oily Components
- Light Assembly
- Engineering
- Repair and Finishing

CERTIFICATION



See overleaf for explanation

PRODUCT INFORMATION

MATERIALS	LINER:	Nitrile
	COATING:	N/A
COLOUR	Black	
LENGTH (mm)	240	
CUFF STYLE	Beaded	

ORDERING DETAILS

SIZE	CODE	PACKAGING
7/S	SKG00724BD	100 singles perbox (90 singles on size XXL)
8/M	SKG00724BF	
9/L	SKG00724BH	
10/XL	SKG00724BJ	
11/XXL	SKG00724BL	
		10 boxes per case

RECOMMENDATIONS FOR USE

- **USE:** Single use glove. Not suitable for mechanical, thermal, heat, electrical, heavy chemical protection. Do not use near moving machines if there is a risk of entanglement.
- **STORAGE:** Store in dry conditions in the original packaging and away from direct sunlight.
- **CLEANING:** To clean, wipe with a damp cloth. Note: The performance characteristics of worn and laundered gloves may differ from the results shown. Inspect the gloves to ensure no damage is present.
- **LIFETIME:** Service life depends on the glove application and therefore cannot be specified. It is the responsibility of user to ensure the glove is suitable for its intended use.

CERTIFICATION LEGENDS



RESISTANCE TO CHEMICAL PERMEATION - EN ISO 374:2016

CODE	CHEMICAL	CODE	CHEMICAL	TYPE OF GLOVES	BREAKTHROUGH TIME
A	Methanol	J	n-Heptane	A	≥30 min for at least 6 chemicals
B	Acetone	K	Sodium hydroxide 40%		
C	Acetonitrile	L	Sulphuric acid 96%		
D	Dichloromethane	M	65% Nitric acid	B	≥30 min for at least 3 chemicals
E	Carbon Disulfide	N	99% Acetic acid		
F	Toluene	O	25% Ammonium hydroxide	C	≥10 min for at least 1 chemical
G	Diethylamine	P	30% Hydrogen peroxide		
H	Tetrahydrofurane	S	40% Hydrofluoric acid		
I	Ethyl acetate	T	37% Formaldehyde		



FOOD CONTACT DIRECTIVE EC 10/2011



PROTECTION AGAINST MICRO-ORGANISMS EN 374-5

VIRUS = Glove has passed ISO 16604:2004 (method B)

EUROPE

www.globusgroup.com

E: sales@globus.co.uk
T: +44 (0)161 877 4747
F: +44 (0)161 877 4746

MIDDLE EAST AND AFRICA

www.globusgroup.com/gcc

E: gcc@globusgroup.com
T: +971 4 882 9962
F: +971 4 882 9963

