



BA310MET-T Trinocular

Fixed 50:50

The BA310MET is an affordable and powerful Metallurgical microscope series of robust Incident light microscopes. Now Industrial quality control can be performed for all opaque materials like minerals and metal samples with ease and efficiency. Also, the BA310MET performs well in Educational environments of engineering and material professions, where affordability and ease-of-use are key demands.

Cat No. 1100100402544

Model	BA310 MET-T Trinocular
Optical System	Colour Corrected Infinity Optical System (CCIS®)
Observation tube	Trinocular head
Interpupillary distance	55-75mm
Trinocular light split	Fixed 50:50 erect image
Inclination	30° inclined
Eyepieces	N-WF10X/20mm with diopter adjustment, +/- 5 diopter, cross reticle on one eyepiece
Nosepiece	Reversed quintuple revolving nosepiece
Objective classification	Infinity Corrected CCIS LM Plan Achromatic, DIN 45mm
Objectives	5X/0.13 (WD 20.3mm), 10X/0.25 (WD 17.5mm), 20X/0.4 (WD 8.1mm), 50X/0.55 (WD 8.4mm)
Objective mounting thread	W 4/5" x 1/36" (RMS standard)
Stage	Mechanical stage, hard coated with built-in low position coaxial stage control
Stage size	240x140mm or 300x180mm
Mechanical stage X&Y range	(Stroke 3"x2") 75x50mm
Upper limit stop	Upper limit stop preset but adjustable
Condenser	Focusable Abbe condenser N.A. 0.85 with iris diaphragm
Focus mechanism	Coaxial coarse and fine focusing system with tension adjustment
Fine Focus precision	2 µm minimum increment
Z-axis movement	30mm
Reflected illumination	Epi-illuminator 12V/50W Quartz Halogen or 3W LED with integrated field and aperture diaphragms and external lamp house
Transformer	External
Power supply	100-240V (CE)
Transmitted illumination	6V/30W Quartz Halogen or 3W LED Koehler illumination with intensity control
Transformer	Internal
Power supply	100-240V (CE)
Accessories included	Blue, frosted, green and yellow filters, power cord, dust cover, and allen key
Dimensions	508x240x465mm
Weight	12.7kg

Add a Moticam camera to capture, document, annotate and share images and videos with the Motic Images Plus 2.0 software.