

HERMLE
Benchmark

Z167-M

Microcentrifuge



- Includes 18 place rotor for 1.5/2.0ml tubes
- High speed, up to 14,000rpm /15,994 xg
- Compact, 11 x 14.5 inch footprint
- NEW, LED status indicator
- Unique EZ-Scroll™ touch pad



Z167 M Summary

Speed up to 14,000 rpm
G-Force up to 15,994 x g

Angle Rotor Capacity

18 x 1.5/2.0 ml

Z167 M Features

Microprocessor Control

- Indication of both set and actual values
- EZ-Scroll™ touch pad
- LED status indicator
- Over-speed protection
- Increments of 10 rpm/50 rcf
- Imbalance detection
- Adjustable Accel/Decel
- Program Storage (up to 99)
- Audible end of run alarm

Maintenance free induction drive
Quiet operation, less than 57 DB
Splash proof display
Sleep mode
Compact, only 11 inches wide
Tool-free rotor removal
Electrical Safety lid-lock

Z167 M Specifications

Speed Range: 200 to 14,000 rpm
Max. RCF: 15,994 x g
Max Capacity: 18 x 1.5/2.0 ml
Timer: up to 99 hr, 59 min.
Dimensions: 11 x 14 x 9.5 in.
(W x D x H) 28 x 35 x 24 cm.
Weight: 26.5 lbs (12 kg)
Electrical: 120 or 230V, 50/60 Hz
Power Draw: 130W

The Z167-M Microcentrifuge is a powerful, compact, easy-to-use high speed microcentrifuge for labs looking to save valuable bench space, but not compromise on speed and power.

The Z167-M's compact design houses a powerful, maintenance free, induction motor that can reach up to 14,000rpm/15,994 xg. The included rotor is an 18-place. Accompanied by Hermle's easy to use control panel, the unique EZ-Scroll™ touch pad, gives you ease of control and a modern feel. Additionally, this model features a color changing LED status indicator that let's you know what operating state the unit is in from a distance. Whether the unit is running, on standby, or in sleep mode, it is easy to tell from a far with this new feature. The advanced microprocessor controls allow for setting/displaying of the rotational speed in either rpm or rcf, in increments of 10. In addition to retrieving saved programs, the easy to use front panel can be used to adjust accel/decel rates, run time, and change the end of run alarm tone. There is also a momentary spin function that will run while the button is pressed and a sleep mode to save energy.

Some of the safety features in the Z167-M include an automatic lid-lock that prevents it from being opened while the rotor is still in motion, a splash proof display, and a unique imbalance detection system designed to automatically power down the motor in the event of improper loading of the rotor, or any tube breakage.

The Z167-M is the perfect microcentrifuge for any lab.

Z167-M*

Z167-M Microcentrifuge with rotor, 120V

*115V with US Plug. For 230V (EU Plug), please order -E.



Includes: Z167-1820

18 x 1.5/2.0ml Angle Rotor (45°)
Max Speed: 14,000 rpm / 15,994 x g
Accel: 14 sec. / Decel: 16 sec.

Inserts/Adapters

C1008-A5-6: 0.5ml Adapter pack, 6/pk.
C1008-A2-6 0.2ml Adapter pack, 6/pk.

NEW feature! LED Status Indicator



Running



Standby



Sleep