


HDV Accessories VideoScope Camera probes & accessories



Ordering

- HDV-TX16mm Articulating VideoScope Camera Head with Macro lens and 1m Semi-Rigid Cable
- HDV-TX1L6mm Articulating VideoScope Camera Head with Long Focus lens and 1m Semi-Rigid Cable
- HDV-WTX16mm Wireless Articulating VideoScope Camera Head w/Macro lens & 1m Semi-Rigid Cable
- HDV-WTX1L6mm Wireless Articulating VideoScope Camera Head w/Long Focus lens & 1m Semi-Rigid Cable
- HDV-TX26mm Articulating VideoScope Camera Head w/Macro lens and 2m Semi-Rigid Cable
- HDV-TX2L6mm Articulating VideoScope Camera Head w/Long Focus lens and 2m Semi-Rigid Cable
- HDV-WTX26mm Wireless Articulating VideoScope Camera Head w/Macro lens & 2m Semi-Rigid Cable
- HDV-WTX2L6mm Wireless Articulating VideoScope Camera Head w/Long Focus lens & 2m Semi-Rigid Cable
- HDV-4CAM-1FM4mm VideoScope Camera Head with Macro lens and 1m Flexible Cable
- HDV-4CAM-5FM4mm VideoScope Camera Head with Macro lens and 5m Flexible Cable
- HDV-5CAM-1FM5.5mm VideoScope Camera Head with Macro lens and 1m Flexible Cable
- HDV-5CAM-3F5.5mm VideoScope Camera Head with long depth of field and 3m Flexible Cable
- HDV-5CAM-3FM5.5mm VideoScope Camera Head with Macro lens and 3m Flexible Cable
- HDV-5CAM-30FM ...5.5mm VideoScope Camera Head with Macro lens and 30m Flexible Cable
- HDV-5CAM-10F5.5mm VideoScope Camera Head with long depth of field and 10m Flexible Cable
- HDV-5CAM-1R5.8mm VideoScope Camera Head with long depth of field and 1m Semi-Rigid Cable
- HDV-5CAM-1RM5.8mm VideoScope Camera Head with Macro lens and 1m Semi-Rigid Cable
- HDV-5CAM-3R5.8mm VideoScope Camera Head with long depth of field & 3m Semi-Rigid Cable
- HDV-5CAM-3RM5.8mm VideoScope Camera Head with Macro lens and 3m Semi-Rigid Cable
- HDV-25CAM-10G ...25mm VideoScope Camera Head with long depth of field and 10m Fiberglass Cable
- HDV-25CAM-30G ...25mm VideoScope Camera Head with long depth of field and 30m Fiberglass Cable
- HDV-WTXWireless Transmitter
- HDV-PCSpare Patch Cable for HDV Series
- ADPTR-HDVReplacement AC Adaptor

