

DYNEO DD-BC26 Heating Circulator

New temperature control technology for demanding applications

DYNEO DD heating circulators for internal and external applications are equipped with closed bath tanks. The tanks are well insulated and include a coil for counter-cooling. An integrated drain tap makes emptying the tank safe and clean. The multilingual 3.5-inch color display and unique rotary knob provide for straightforward and intuitive operation.



Your advantages

- Suitable for internal and external applications
- Powerful and infinitely adjustable pressure pump
- Flow rate 22 l/min, pressure 0.6 bar
- Easy switching between internal and external circulation
- Large color TFT display, multilingual interface
- Central rotary knob (controller) simplifies operation
- Integrated programmer for 8 x 60 program steps
- Integrated external Pt100 connection
- USB port
- RS232 interface or analog interfaces
- Bath cover included with delivery
- Integrated drain makes emptying liquid easy and safe.
- High-quality thermal insulation of the bath tank

Technical Data

Order No.	9021526
Order No. with RS232 Option	9021526.D
Order No. with analog Option	9021526.A
Model series	DYNEO
Category	Heating Circulators
Working temperature range (°C)	+20 ... +200
Temperature stability (°C)	±0.01
Setting / display resolution	0.01 °C
Temperature Display	3.5" TFT Display
Heating capacity (kW)	2
Pump capacity flow rate (l/min)	8 ... 23
Pump capacity flow pressure (bar)	0.1 ... 0.6
Viscosity max. (cSt)	50
Bath opening / bath depth (W x L / D cm)	26 x 35 / 20
Pump connections	M16x1
Barbed fittings diameter (inner dia. / mm)	8 / 12
Filling volume liters	19 ... 26
Ambient temperature	5...40 °C
Dimensions W x L x H (cm)	39 x 62 x 48

Weight (kg)	18.7
Included with each unit	2 each barbed fitting for tubing 8 and 12 mm inner dia. (pump connections M16x1 male)
Cooling coil	integrated
Bath tank	Stainless steel
Bath cover	integrated
Available voltage versions	200-230V/50-60Hz 100-115V/50-60Hz

Characteristics



Analog I/O.

Analog interfaces for integration into process control systems (optional).



Powerful. Adjustable.

Strong pressure pump, continuously adjustable.



ATC3 Calibration.

'Absolute Temperature Calibration' for compensating a physically caused temperature difference, 3-point calibration.



Process stability.

Early warning - visual and acoustic - of critical states increases process stability.




Brilliance. In color.

Large color display with vivid luminance is easy to read, even from a large distance.



Process. Under control.

Full control of the dynamic, access to all important control parameters for individual process optimisation.



Condensation protection.

Superb design solution. Integrated ventilation directs air over the bath lid and minimizes condensation.



Programmer. Integrated.

The integrated internal programmer makes it possible to automatically run temperature time profiles.



Connection. Easy.

Inclined pump connections (M16x1) facilitate the connection of applications. Each unit includes 2 barbed fittings of 8/12 mm diameter each.



RS232.

Standard connection using the optional serial RS232 interface.




Everything at the front.

All operating controls and safety functions are accessed easily and comfortably from the front.



Stable. Mobile.

Rubber feet keep JULABO Circulators standing firm. Larger and more powerful units also have integrated rollers for easy handling.



Fill level. Monitored.

Fill level indicator on the display for heat-transfer liquid.



Temperature. Under control.

External Pt100 sensor connection for precise measurement and control directly in the external application.



Highly precise.

PID Temperature control with drift compensation and adjustable control parameters, temperature stability ± 0.01 ... ± 0.02 °C.



Turn. Push. Go.

Easy operation of all parameters using the central controller.



Information. Everything clear.

Information in plain text on a large color screen.



USB.

Remote control made easy using the integrated USB interface.