

# OTS60SX/2

## Semi automatic oil test set



- **Robust oil chamber lid, fully opening for easy access**
- **Robust and protective control panel lid**
- **Lightweight portable unit for field use**
- **Simple, semi-automatic operation**
- **Suitable for all oil breakdown testing to 60 kV**
- **Automatic 1 minute timer for easy withstand testing**
- **1ms HV switch off time eliminates damage to the oil samples**

### DESCRIPTION

The Megger® OTS60SX/2 is a lightweight, semi-automatic, oil dielectric strength test set. The instrument is suitable for field use and can be powered from a range of mains supplies. The maximum 60 kV output allows tests to be performed on oil from a wide variety of electrical installations including transformers, circuit breakers and other equipment. The operation of the test set is extremely simple and the results are displayed on a bright LED display. A selection of vessels allows the instrument to be configured for a variety of test standards.

The microprocessor controlled, semi automatic operation allows the user to select a choice of voltage rise rates as specified in many national standards. The start button will then initiate the test. If oil breakdown occurs the instrument will remove the test voltage and display the breakdown value. Alternatively the user can pause the test voltage at any time to carry out a withstand test. The voltage will be maintained at this level for one minute or until breakdown. After one minute the voltage will automatically continue to rise until breakdown occurs or to the maximum output of the instrument.

A sheet steel enclosure makes the instrument rugged and safe. A strong polycarbonate window covers the high voltage chamber. A mesh screen enables the oil breakdown to be viewed and reduces electro-magnetic emissions. Operator safety is ensured by an interlock on the chamber door. The power cord and other accessories are stored in a pouch which is fitted to the side of the test set. An optional carrying bag with shoulder strap is also available.

The oil vessel is located in the top of the instrument. An external nut varies the electrode gap. The design of the vessels and test chamber makes them easy to clean. The instrument is supplied with a spacing gauge for setting the electrode gap.

A range of vessels are available suitable for testing to a wide range of national specifications. Three types of electrode are available; spherical (IEC type), mushroom (VDE/ASTM D1816) and cylindrical (ASTM D877). The oil sample can be stirred by a motor driven propeller available in some of the vessels. Spare electrodes can also be supplied suitable for all types of oil testing.

### APPLICATION

Oil has been used as an insulating medium in transformers for over one hundred years. From the earliest days of transformer design, oil has been recognised as being an efficient coolant with a high flash point and high electric strength. Oil can be used in electrical equipment for a long time if adequately maintained.

Many factors can lead to a weakening of the insulation properties of oil. Oil degradation takes place due to oxidation, acids, sludge, gas and water absorption. These processes change the electrical properties of the oil which can be seen from a dielectric strength test.

The range of oil test sets available from Megger offers solutions for all oil testing applications. The popular portable OTS60PB, OTS80PB and laboratory OTSAF/3 series are fully automatic oil testers that incorporate a built in printer and enable the user to program custom tests.

## FEATURES AND BENEFITS

- Simple to use
- Robust and protective metal lid for easy transport
- Low cost, low weight (17 kg) (37.5 lbs)
- Strong, safe construction
- Suitable for testing to national standards
- Auto 1 minute timer for easy with stand testing
- 0,1 kV measurement resolution
- Large, clear LED display
- Reliable operation controlled by microprocessor
- Powered from a range of mains supplies
- Wide range of optional vessels
- Easy to clean vessel and chamber

## SPECIFICATION

<b>Output voltage</b>	Voltage: 0 - 60 kV Test Frequency: 61,8 Hz Transformer rating: 500 VA
<b>Output disconnection</b>	Within 1 ms of detection of breakdown
<b>Power supply</b>	115/230 V, switch selectable (99-132 V, 198-264 V) 50/60 Hz, max 80 VA
<b>Operation</b>	Semi automatic with selectable 500/2000/3000 V/s voltage rise rate Pause function with automatic 1 minute timer for withstand testing
<b>Start/stop</b>	Start, pause, stop & ramp rate select
<b>Display</b>	0,0 - 60,0 kV 25 mm LED digital display 'HV On' LED
<b>Display accuracy</b>	2% ± 3 digits
<b>Safety</b>	The instrument meets the requirements of IEC61010-1
<b>EMC</b>	In accordance with IEC61326-1
<b>Fuse</b>	250 mA (T) HRC to IEC127/5 for 220/240 V supply 500 mA (T) HRC to IEC127/5 for 110/120 V supply
<b>Operating temperature range and humidity</b>	0 to 40°C (32 to 104°F) 80% RH at 40°C (104°F)
<b>Storage temperature range and humidity</b>	-20 to +70°C (-4 to +158°F) 93% RH at 40°C (104°F) 95% RH at 25°C (77°F)
<b>Dimensions</b>	380mm (H) x 401mm (W) x 260mm (D) (15 in. x 15,8 in. x 10,2 in.)
<b>Weight</b>	17 kg (37.5 lbs)

## ORDERING INFORMATION

Description	Order Code	Description	Order Code
OTS60SX/2 Semi Automatic 60 kV Oil Test Set	1005-272	0,5 l Vessels with Spherical electrodes for IEC 156 with stirrer	6320-236
<b>Included Accessories</b>		0,5 l Vessels with Mushroom electrodes for VDE0370	6320-234
Spacing Gauge (0,5 mm x 6)	6132-009	0,5 l Vessels with Mushroom electrodes for ASTM D1816 with stirrer	6320-237
Accessory Pouch	6320-232	0,5 l Vessels with 0.15 litre vessel with cylindrical electrodes for ASTM D 877	6111-356
User Guide	6172-120	<b>Spare electrodes for 0.5 L vessels</b>	
Supply lead for battery charger	25424-860	Spherical (pair)	6220-484
AC power lead - US	25970-002	Mushroom (pair)	6220-580
<b>Optional Accessories</b>		Cylindrical (pair)	6220-483
Spare Electrodes for 0.5 L vessels	6420-106	Cylindrical with 0,5 mm edge radius (pair)	6220-538
Padded carrying case	6420-106		
0,5 l Vessels with Spherical electrodes for IEC 156	6320-233		

**UK**  
Archcliffe Road Dover  
CT17 9EN England  
T +44 (0) 1304 502101  
F +44 (0) 1304 207342  
UKsales@megger.com

**UNITED STATES**  
4271 Bronze Way  
Dallas TX 75237-1019 USA  
T 800 723 2861 (USA only)  
T +1 214 333 3201  
F +1 214 331 7399  
USsales@megger.com

**OTHER TECHNICAL SALES OFFICES**  
Valley Forge USA, College Station USA,  
Sydney AUSTRALIA, Danderyd SWEDEN,  
Ontario CANADA, Trappes FRANCE,  
Oberursel GERMANY, Aargau SWITZERLAND,  
Kingdom of BAHRAIN, Mumbai INDIA,  
Johannesburg SOUTH AFRICA, Chonburi THAILAND

**CERTIFICATION ISO**  
Registered to ISO 9001:2000 Cert. no. Q 09290  
  
**OTS60SX2\_DS\_EN\_VO1**  
[www.megger.com](http://www.megger.com)  
Megger is a registered trademark