


## Waterbath


# WTB6

Ideal for the temperature control of ointments, emulsions, samples, plates and nutrient solutions in the laboratory, as well as warm storage and calibration in the industrial segment



On this page, you can find all the essential technical data on the Memmert water bath. Our customer relations team will be pleased to help if you want further information. If you should require a customised special solution, please contact our technical specialists at <a href="mailto:sales@memmert.com">sales@memmert.com</a>.





Temperature	T	ei	n	p	e	ra	tι	ır	е
-------------	---	----	---	---	---	----	----	----	---

Temperature sensor	digital temperature sensor, mounted on the outside of the bath
Temperature	Setting Celsius / Fahrenheit
Working temperature range	at least 5 above ambient to +100 (depending on ambient pressure)
Setting temperature range	+10 to +100 °C
Setting accuracy temperature	0.1 °C

# **Control technology**

Calibration	2-point calibration	
Controller	intuitive 3.5" colour graphic display with touch screen	
Controller	digital display of set and actual temperature and of (remaining) programme time	

## Safety

Temperature control Temperature control	two-stage safety system to prevent overtemperature individually adjustable overtemperature alarm, visual and acoustic
Temperature control	Independent temperature limiter to switch off the heating in case of failure
Autodiagnostic system	microprocessor PID-temperature controllerwith integrated autodiagnostic system withfault indicator

# **Heating concept**

**Heating** corrosion-proof large-area heating on the outside of the interior

# Standard equipment

Drain system	innovative drain system - easy to empty
Timer	digital timer from 1 min. up to 99 hours 59 min., visual and acoustic

#### Stainless steel interior

Dimensions W x H x D in mm         w <sub>(A)</sub> x h <sub>(C)</sub> x d <sub>(B)</sub> : 277 x 150 x 217 mm           Volume         7 l           Liquid level min.         40 mm	Interior	Deep-drawn stainless steel tray (stainless steel W.St. 1-4301), without corners and edges for easy cleaning incl. central drain (no disturbing installations)
		w <sub>(A)</sub> x h <sub>(C)</sub> x d <sub>(B)</sub> : 277 x 150 x 217 mm
Liquid level min. 40 mm	Volume	7
	Liquid level min.	40 mm

## Textured stainless steel casing

Dimensions	$W_{(D)} \times h_{(E2)} \times d_{(E)}$ : 349 x 348 x 289 mm
------------	---

#### **Electrical data**

Voltage Electrical load	230 V, 50/60 Hz approx. 1000 W	
Voltage Electrical load	115 V, 50/60 Hz approx. 1000 W	

#### **Ambient conditions**

Installation	The vent openings in the left and back side must remain unobstructed. Minimum wall spacing on all sides is 80 mm. The minimum spacing from the top of the bath to the next ceiling is 750 mm.	
Ambient temperature	+5 °C to +40 °C	
Humidity rh	max. 80 %, non-condensing	
Overvoltage category	II	
Pollution degree	2	

## Packing/shipping data

Transport information	The appliances must be transported upright
Customs tariff number	8419 8998
Country of origin	Federal Republic of Germany
WEEE-RegNo.	DE 66812464
Dimensions approx incl. carton	w x h x d: 570 x 450 x 420 mm
Net weight	approx. 6 kg
Gross weight carton	approx. 10 kg

# Standard units are safety-approved and bear the test marks

