

NEXT
GENERATION



icountLaserCM30

Particle Contamination Monitor



ENGINEERING YOUR SUCCESS.

Meet the Next Generation

Particle Contamination Monitor - LCM30

The Parker icountLaserCM30 is a next generation fluid system contamination monitoring offering an under 90 seconds test procedure. Multi standard ISO 4406, NAS 1638, AS4059 & GOST cleanliness reporting, data entry and integral printing are all featured on this next generation contamination monitor.

Parker listened to their existing customers and then to the engineers and maintenance operatives to find out the features that have helped make the icountLaserCM a unique predictive maintenance instrument.



What's New...

- Auto testing – start test from hand set
- Shorter test time - under 90 seconds
- Updated main enclosure
- Enhanced handset design
- Refined user interface
- Improved rechargeable battery life
- Integrated RH% moisture sensor and temperature
- Thermal printer (long life) improved data recording
- 8 x reported sizes (6 x measured / 2 x calculated) reporting codes to ISO4406 - NAS1638, AS4059 & GOST
- Now with RS232 Data Transfer over USB
- Easy to use 'Clip On' battery pack



What's in the Case

| | |
|---|--|
| 1 | Particle Contamination Monitor |
| 1 | Rechargeable Battery Pack |
| 2 | Printer Paper Roll (1 x fitted / 1 x spare) |
| 1 | USB cable |
| 1 | Flash Drive Memory Stick (inc. Manual and Download Software) |
| 1 | Quick Start Guide |
| 1 | Power Supply & Regional Power Cable |

Why On-Site Fluid Contamination Monitoring?

- Certification of fluid cleanliness levels.
- Early warning instrument to help prevent catastrophic failure in critical systems.
- Comparable results to Laboratories
- To comply with customer cleanliness requirements and specifications.
- New equipment warranty compliance.
- New oil cleanliness testing.



Features & Benefits

- Special 'diagnostics' are incorporated into the icountLaserCM30 microprocessor control to ensure effective testing.
- Routine contamination monitoring of oil systems and liquid fuels with icountLaserCM30 saves time and saves money.
- Contamination monitoring is now possible during application operation - icountLaserCM30 saves on production downtime.
- Data entry allows individual equipment test log details to be recorded.
- Data retrieval of test results from memory via hand set display.
- Automatic test cycle logging of up to 1000 tests can be selected via hand set display.
- Totally portable, can be used as easily in the field as in the laboratory.
- Automatic calibration reminder.
- Instant results achieved with a test cycle in under 90 seconds.
- Data entry allows individual equipment footprint record.
- Auto 99 test logging, set up via hand set.
- Worldwide service and technical support.
- Re-calibration - Annual certification by an approved Parker Service Centre.



Principle of Operation

The icountLaserCM30 is a Particle Contamination Monitor (PCM) that automatically sizes and counts individual particles suspended in a fluid using a laser illuminated optical light extinction principle.

The sensor uses a focused light source that is projected through oil moving in a flow cell; any particulate contamination within the oil will cause a change in signal proportional to its size on the detector. On-board flow metering delivers a precise volume of fluid through a flow cell at a controlled rate. Focused laser light is projected through fluid in the flow cell and any particulate contamination within the fluid reduces the amount of light that reaches the detector. The signals are processed and the particle size distribution is reported to the user.

Particle sizes are reported in micrometres (1×10^{-6} metres) and displayed as "µm" for ISO Medium Test Dust (MTD) calibration or "µm" for Air Cleaner Fine Test Dust (ACFTD) calibration.

LCM30 Technical Specification

Measurement

| Part Number | Description |
|---|--|
| Particle Size Reporting Channels ⁱ | MTD: >4, >6, >14, >21, >25e, >30, >38 and >70e µm ACFTD: >2, >5, >10, >15, >20e, >25, >50 and >100e µm |
| Reporting Contamination Standards ⁱⁱ | ISO 4406:Code 0 to 22 NAS 1638 0 to 12 GOST 17216:00 to 17 (consult Parker) SAE AS 4059F Table 1: 00 to 12 SAE AS 4059F Table 2: 00 to 12 |
| Other Test Methods | IP564: determination of the level of cleanliness of aviation turbine fuel Automatic IP564 test mode to include single flush and three repeat tests - average and individual results displayed. |
| Reporting Repeatability. | Measured Channels: <7% at measured counts for MTD particles size 4, 6 and 14 µm ⁱⁱⁱ |
| Calibration | MTD: Calibration in accordance with ISO 11943:Section 9 ACFTD: The LCM30 is calibrated against the Master PCM at the particle sizes shown within the specified limits Consult Parker for re-calibration. |
| Test Time | < 90 seconds in both single and multi-test mode. |
| Test Modes | Single / Multiple – fully automated. |
| Moisture Sensor | Compatible with mineral oils only. Relative Humidity (%RH) ±5% RH Stability: +2% RH typical at 50% RH in one year. Temperature [°C] -25 to +150°C ±0.9% |

ⁱ = calculated channel indicated by the letter e on the handset display.

ⁱⁱ = The instrument only uses the shorthand in these standards for reporting contamination levels.

ⁱⁱⁱ = 95% confidence level using an MTD distribution with a concentration of 6mg/L.

LCM30 - Technical Data (cont)

Operating environment

| | |
|---------------------------|--|
| Fluid Compatibility | Mineral oils and petroleum based fluids. For other fluids consult Parker |
| Working Viscosity | 2 to 100 cSt 2 to 200 cSt when used with LCM30 Case Mounted Pump (100 cSt when reporting in GOST standard and using Heated Bath) 2 to 500 cSt when used with Single Point Sampler Higher viscosities when used with Trace Heated Hoses |
| Environmental Temperature | +5°C to +40°C |
| Fluid Temperature | +5°C to +80°C |
| Working Pressure | 2.5 bar when using Case Mounted Pump; up to 420 bar when CMP not used |
| Flow Rate | 30mL/min when using Case Mounted Pump; 6 - 380 l/min max. when used with System 20 Sensors, higher with Single Point Sampler |
| Inlet and Outlet Fittings | M16 MINIMESS® |

Electrical

| | |
|---------------------------|--|
| Instrument External Power | 10 to 24V - 3A max. |
| Trace Heated Hose (THH) | 12V DC 5A max - 24V DC 2.5A max. |
| Rechargeable Battery | 12V / Capacity: 4.5Ah with - 12V Nom. |
| Rechargeable Battery Pack | Input Voltage: 18V DC - Input Current: 2.5A Charge Time: Typically 4.0 hours for full charge Number of Tests: Typically 320 - 450 depending on product variant and operating conditions. |
| Regional Plugs | UK (Type G) - EU (Type C) - US (Type B) - Australasia (Type I) |

Interface

| | |
|---------------------------|---|
| Data Communication Port | USB B |
| Menu Structure and Layout | Intuitive menu structure |
| Case Mounted Pump (CMP) | CMP operation via handset - Automatic CMP operation when test enabled |
| Trace Heated Hose (THH) | Trace Heated Hose (THH) initiated via hand set. |
| Printer | Thermal printer |

Materials

| | |
|---------------------------|--|
| Outer Mouldings | Mouldings: Structural foam ABS / Coating: Polyurethane |
| Material Wetted Flow Path | Nylon with Kevlar Reinforcement Microbore Hose / Brass / Viton / Polyacetal (Delrin) / Zinc Plated Mild Steel / Stainless Steel 302, 303 and 316 / Soda-lime Glass |

Standard product table

| | |
|-----------|---|
| LCM302022 | icountLCM30 (MTD calibration) |
| LCM302028 | icountLCM30 (MTD calibration) (Case Mounted Pump) |
| ACC6NA006 | Printer Paper Rolls (pack of 5) |
| ACC6NA001 | LCM30 Rechargeable Battery Pack |

Supporting Products

Universal Bottle Sampler

Simple and efficient offline oil sampling

The UBS provides the dynamic link to portable particle and water counters. The UBS off-line sampler has microprocess technology to recognise and adjust to the connecting monitor including the icountLCM30 and H₂Oil water in oil monitor.



| Part Number | Description |
|-------------|--|
| UBS9002 | Universal bottle sampler (includes aluminium case and accessories) |
| UBS9003 | Universal bottle sampler |

Single Point Sampler

Lightweight and compact connection

The SPS (Single Point Sampler) is a lightweight, compact and easy to use online sampling unit that connects an icountLCM30 or H₂Oil to a single pressure test point in a fluid system. Suitable for use with mineral and biodegradable oils, petroleum based fluids, the SPS offers fingertip operated control even at high pressures - 420 bar (6000 PSI) rated maximum pressure.



| Part Number | Supersedes | Description |
|-------------|------------|---|
| SPS2021 | SPS.2021 | Single point sampler (Mineral Oil fluids) |
| ACC6NW003 | B84784 | Waste bottle (Universal) |
| ACC6NH001 | B84224 | Extension hose/coupling (Mineral fluids) |
| ACC6NH003 | B84788 | Waste hose (Mineral Oil) |

Parker Worldwide

Europe, Middle East, Africa

AE – United Arab Emirates,

Dubai

Tel: +971 4 8127100

AT – Austria, St. Florian

Tel: +43 (0)7224 66201

AZ – Azerbaijan, Baku

Tel: +994 50 2233 458

BE/NL/LU – Benelux,

Hendrik Ido Ambacht

Tel: +31 (0)541 585 000

BY – Belarus, Minsk

Tel: +48 (0)22 573 24 00

CH – Switzerland, Etoy

Tel: +41 (0)21 821 87 00

CZ – Czech Republic,

Prague

Tel: +420 284 083 111

DE – Germany, Kaarst

Tel: +49 (0)2131 4016 0

DK – Denmark, Ballerup

Tel: +45 43 56 04 00

ES – Spain, Madrid

Tel: +34 902 330 001

FI – Finland, Vantaa

Tel: +358 (0)20 753 2500

FR – France, Contamine s/Arve

Tel: +33 (0)4 50 25 80 25

GR – Greece

Tel: +30 69 44 52 78 25

HU – Hungary, Budaörs

Tel: +36 23 885 470

IE – Ireland, Dublin

Tel: +353 (0)1 466 6370

IL – Israel

Tel: +39 02 45 19 21

IT – Italy, Corsico (MI)

Tel: +39 02 45 19 21

KZ – Kazakhstan, Almaty

Tel: +7 7273 561 000

NO – Norway, Asker

Tel: +47 66 75 34 00

PL – Poland, Warsaw

Tel: +48 (0)22 573 24 00

PT – Portugal

Tel: +351 22 999 7360

RO – Romania, Bucharest

Tel: +40 21 252 1382

RU – Russia, Moscow

Tel: +7 495 645-2156

SE – Sweden, Borås

Tel: +46 (0)8 59 79 50 00

SL – Slovenia, Novo Mesto

Tel: +386 7 337 6650

TR – Turkey, Istanbul

Tel: +90 216 4997081

UK – United Kingdom, Warwick

Tel: +44 (0)1926 317 878

ZA – South Africa, Kempton Park

Tel: +27 (0)11 961 0700

North America

CA – Canada, Milton, Ontario

Tel: +1 905 693 3000

US – USA, Cleveland

Tel: +1 216 896 3000

Asia Pacific

AU – Australia, Castle Hill

Tel: +61 (0)2-9634 7777

CN – China, Shanghai

Tel: +86 21 2899 5000

HK – Hong Kong

Tel: +852 2428 8008

IN – India, Mumbai

Tel: +91 22 6513 7081-85

JP – Japan, Tokyo

Tel: +81 (0)3 6408 3901

KR – South Korea, Seoul

Tel: +82 2 559 0400

MY – Malaysia, Shah Alam

Tel: +60 3 7849 0800

NZ – New Zealand, Mt Wellington

Tel: +64 9 574 1744

SG – Singapore

Tel: +65 6887 6300

TH – Thailand, Bangkok

Tel: +662 186 7000

TW – Taiwan, Taipei

Tel: +886 2 2298 8987

South America

AR – Argentina, Buenos Aires

Tel: +54 3327 44 4129

BR – Brazil, Sao Jose dos Campos

Tel: +55 080 0727 5374

CL – Chile, Santiago

Tel: +56 22 303 9640

MX – Mexico, Toluca

Tel: +52 72 2275 4200



EMEA Product Information Centre

Free phone: 00 800 27 27 5374

(from AT, BE, CH, CZ, DE, DK, EE, ES, FI, FR, IE, IL, IS, IT, LU, MT, NL, NO, PL, PT, RU, SE, SK, UK, ZA)

US Product Information Centre

Toll-free number: 1-800-27 27 537

www.parker.com