



**Awarded one of  
MOTOR Magazine's  
TOP 20 NEW TOOLS for 2011!**

**The Reichert Digital DEF-Chek®...  
the fast, accurate, state-of-the-art  
digital instrument for testing  
Diesel Exhaust Fluid (DEF)**

***Clean exhaust systems for cleaner air.***

Selective Catalytic Reduction (SCR) systems for diesel automobiles, trucks, buses, and off road equipment require pure Diesel Exhaust Fluid at an exact concentration of **32.5%** urea in deionized water. This fluid is known as DEF, AdBlue®, ARLA, and AUS 32. Any other concentration compromises the SCR system, which fails the regulatory requirements of governmental agencies such as the EPA, European Commission, and MLIT.

***Reichert DEF-Chek®: digital, state-of-the-art  
protection for your SCR system.***


The Reichert **DEF-Chek®** digital instrument accurately measures DEF for the right urea content detecting whether the fluid will do its job in the exhaust system. The world's smallest scientific DEF testing device offers quick, automatic digital measurements in seconds and provides over 10,000+ measurements on two AAA batteries. The Reichert **DEF-Chek®** was chosen by MOTOR magazine as a *MOTOR Top 20 Tools Award*.



**Reichert®**  
TECHNOLOGIES

*Analytical Instruments • Automotive & Truck*

**Maintain  
optimal SCR  
performance and  
keep rolling  
at 32.5%  
concentration,  
100% of the time**



**www.ReichertAutoTech.com**



## The Reichert DIGITAL DEF-Chek®

### SPECIFICATIONS:

|                                    |                                                                          |
|------------------------------------|--------------------------------------------------------------------------|
| Catalog Number                     | 13940013                                                                 |
| Measurement Method                 | Digital Refractometer                                                    |
| Reading Scale                      | DEF/AdBlue®/ARLA/AUS32 - Diesel Exhaust Fluid, % urea in deionized water |
| Reading Range                      | 0.0 to 50.0% urea concentration by weight (w/w)                          |
| Accuracy                           | +/- 0.1%                                                                 |
| Calibration                        | Distilled Water                                                          |
| Automatic Temperature Compensation | 68°F (20°C)                                                              |
| Illumination                       | 589nm LED                                                                |
| Dimensions                         | 54 x 27 x 100 mm / 2.1 x 1.1 x 3.9 inches                                |
| Weight                             | 3.5 ounces (100 grams)                                                   |
| Comfort/Ergonomics                 | Detachable neck lanyard and rubber side grips for ease of handling       |
| Power                              | 2 AAA Batteries, included                                                |
| Power Management                   | 10,000 readings, Auto-Off Sleep Mode                                     |
| Ratings                            | IP65 Dust proof/Water Resistant, CE, RoHS, and WEEE compliant.           |
| Factory Warranty                   | One Year                                                                 |
| Accessory Holster case             | (cell phone type) available – Catalog 13941000                           |

### Leave the science to Reichert.

With the simple push of a button, the Reichert Digital **DEF-Chek®**, the world's smallest handheld digital tester, will quickly and accurately measure the % concentration of Urea in deionized water, commonly referred to as Diesel Exhaust Fluid. Diesel powered vehicles are required to meet new strict EPA, European Commission, and MLIT standards regarding tailpipe emissions. The technology of Selective Catalytic Reduction (SCR) has been adopted by the major manufacturers to address this requirement. In the European market, this SCR technology using AdBlue® (Diesel Exhaust Fluid) has been accepted and utilized for many years. Diesel Exhaust Fluid (DEF) is injected into the exhaust gasses as a mist before it passes through the catalyst. The catalyst and DEF converts harmful and polluting Nitrogen Oxide (NOx) into harmless nitrogen and water vapor. For this technology to work, the Urea in the deionized water must have an exacting concentration of 32.5%. Any deviation from this Urea concentration will adversely affect this technology. With the growth of SCR equipped diesel engines, automobile and truck dealerships, service centers, trucking fleets, service stations, and truck stops are using Diesel Exhaust Fluid, and it is important to insure the quality of the DEF is maintained throughout the supply chain.

### Avoid costly repair bills and fines!

The Reichert Digital **DEF-Chek®** tester detects changes in the concentration caused by water dilution and adulteration. Check the concentration of Diesel Exhaust Fluid (DEF) like you would check the concentration of engine coolant (Antifreeze). Both DEF and engine coolant have been chemically formulated to work effectively at a specific concentration. **An incorrect concentration will result in potential costly damage** to the SCR system (injectors) and failing the emissions standards set by government agencies.

#### Reichert DIGITAL DEF-Chek®

| Part#    | Description                      |
|----------|----------------------------------|
| 13940013 | DEF-Chek® digital model (% Urea) |



#### Reichert DIGITAL Multi-Chek®

| Part#    | Description                            |
|----------|----------------------------------------|
| 13940014 | Multi-Chek® digital model (Fahrenheit) |
| 13940015 | Multi-Chek® digital model (Celsius)    |



#### Reichert DIGITAL Brake-Chek®

| Part#    | Description                            |
|----------|----------------------------------------|
| 13940016 | Brake-Chek® digital model (Fahrenheit) |
| 13940017 | Brake-Chek® digital model (Celsius)    |



#### Reichert DIGITAL Glycerin, EG, PG-Chek

| Part#    | Description                              |
|----------|------------------------------------------|
| 13940022 | Glycerin-Chek digital model (Fahrenheit) |
| 13940023 | Glycerin-Chek digital model (Celsius)    |
| 13940024 | EG-Chek digital model (Fahrenheit)       |
| 13940025 | EG-Chek digital model (Celsius)          |
| 13940026 | PG-Chek digital model (Fahrenheit)       |
| 13940027 | PG-Chek digital model (Celsius)          |



Analytical Instruments • Refractometers

**Corporate Office**  
Reichert Technologies  
3362 Walden Avenue  
Buffalo, New York 14043 USA  
Tel. +1 716-686-4500  
Fax. +1 716-686-4545  
Toll Free USA 1-888-849-8955

e-mail:  
reichertai.refractometers@ametek.com  
[www.ReichertAutoTech.com](http://www.ReichertAutoTech.com)

**European Service Center**  
Carl-von-Linde-Str. 42 85716  
Unterschleissheim / Munich  
Germany  
Tel: +49 (89) 315 8911 0  
Fax: +49 (89) 315 891 99

Reichert Technologies is a division of  
**AMETEK®**  
ULTRA PRECISION TECHNOLOGIES

[www.ReichertAutoTech.com](http://www.ReichertAutoTech.com)