



# 395 Handheld Refractometer

## APPLICATIONS

### HVACR:

- Radiant Heat Line Fluids For walkways, garages, closed loop systems, and in-floor systems

### AUTOMOTIVE:

- Engine coolants
- Battery fluid condition
- Recreational vehicles

### PLUMBING:

- Battery condition of sump pump battery back up systems

Turn over for technical information and accessory part numbers.

The Value Leader™

## The 395 Handheld Refractometer

is designed to give an accurate reading regarding the freezing point of fluids used in hydronic heating systems. It is quick and easy to use. Place a drop of fluid on the prism, close the plastic lid, and look through the eye piece. Where the blue and white colors meet indicates the freezing point of the coolants or the state of charge for batteries.



## FEATURES

- Use to test the following liquids:
  - Propylene glycol
  - Ethylene glycol
  - Battery fluid
- Does not degrade like litmus paper; Allows for more accurate readings
- Easy viewing: cushioned eye piece adjusts to most visual needs.
- Smooth focus adjustment for reliable repeat testing

The above information is provided to the best of TPI's knowledge and is not guaranteed. The above information is subject to change at any time.

visit us at [www.tpi-thevalueleader.com](http://www.tpi-thevalueleader.com)



**TECHNICAL SPECIFICATIONS AND ACCESSORIES**

- Digital Multimeters
- Clamp Meters
- Hand-held Oscilloscopes
- Refrigerant & Combustible Gas Leak Detectors
- Temperature Testers
- BNC Coax Cable Connectors
- Test Leads
- Accessories

**Test Products International, Inc.**  
 Headquarters:  
 9615 SW Allen Blvd.  
 Beaverton, OR 97005  
 USA  
 503-520-9197  
 Fax: 503-520-1225  
 email:  
 info@tpi-thevalueleader.com

**Test Products International, Ltd.**  
 342 Bronte St. South  
 Unit 9  
 Milton, Ontario L9T  
 5B7  
 Canada  
 905-693-8558  
 Fax: 905-693-0888  
 email:  
 info@tpicanada.com

**Test Products International UK Ltd.**  
 Longley House, East Park  
 Crawley, West Sussex  
 RH10 6AP England  
 Tel: +44 (0)1293 561212  
 Fax: +44 (0)1293813465  
 contactus@tpieurope.com

# 395 Handheld Refractometer

## 395 SPECIFICATIONS

Calibration	Field calibrateable using distilled water
Liquid and Range	Propylene Glycol: -60°F to 20°F (-50°C to -5°C) Ethylene Glycol: -60°F to 20°F (-50°C to -5°C) Battery Fluid: 1.10 to 1.4 pH with recharge, fair, and good ratings
Dimensions	6 3/8" x 1 1/4", 7/8" tube diameter
Weight	.6lbs (.286kg)
Standard Accessories	Refractometer Calibration screwdriver Eyedropper Distilled water Protective plastic case

### TDS / Salt Meter 390



- Test condensate water in cooling tower and humidifier reservoir applications to prevent bacterial growth
- Test TDS levels in make-up water to prevent scale formation, corrosion, and embrittlement
- Reduce water and chemical consumption in boilers and cooling towers
- Determine when to perform blowdown and add make-up water
- Prevent contamination and corrosion of control valves, heat exchangers, and steam traps
- Verify automated TDS controllers are functioning properly
- Prevent low quality wet steam generation in boilers due to foaming caused by high TDS levels

### Distributed By:



To learn about the entire line of TPI products visit:

[www.tpi-thevalueleader.com](http://www.tpi-thevalueleader.com)

L 395-0107  
 Copyright © 2007 Test Products International, Inc.