



a xylem brand

**YSI 3100 and 3200 Laboratory Benchtop Meters**

Accurate Instruments for Conductivity Testing



**YSI 3200 Conductivity System - Unmatched for UltraPure Water**

- User-selected measurement mode: conductivity, temperature, resistivity, conductance, salinity, resistance, or total dissolved solids
- RESISTANCE RATIO TECHNOLOGY™ provides unmatched accuracy for ultrapure water
- Multipoint calibration; variety of measurements with the same cell
- High and low alarms for process applications
- Linear and nonlinear temperature compensation

**YSI 3100 Conductivity - High Accuracy**

The YSI 3100 provides high-accuracy measurements for basic conductivity. Includes direct-reading digital display, adjustable temperature coefficient, and automatic temperature compensation.



3200 series cells with built-in temperature sensors (see chart on back)

**Conductivity Cells - Automatic Temperature Compensation**

YSI 3200 Series Conductivity Cells have built-in thermistors, allowing automatic temperature compensation. All YSI cells are calibrated according to OIML (International Organization of Legal Metrology) recommendations 56 (Standard solutions reproducing the conductivity of electrolytes) and 68 (Calibration method for conductivity cells).

- Shipped with greater than 1% cell accuracy; includes certificate of traceability
- Can be used as a secondary lab standard
- Cells can be re-calibrated (adjusted) to NIST traceable standards; YSI offers this service with a certificate of calibration and traceability
- Black platinum electrodes are extremely stable and linear; can be replatinized using the instrument


**Resistor Set Verifies Performance**

The 3166 Resistor Set tight-tolerance calibrators are more precise than common resistors and can verify meter performance. Six resistors included.

**NIST Traceable Calibrator Solutions for Highest Accuracy**

To assure quality, YSI inspects them with reference to primary standard solutions according to OIML recommendation 56. Bottles include a table of corrections at temperatures between 20 and 30°C.

YSI 3161	1,000 $\mu\text{S}/\text{cm}$	$\pm 0.50\%$ tolerance	1 quart
YSI 3163	10,000 $\mu\text{S}/\text{cm}$	$\pm 0.25\%$ tolerance	1 quart
YSI 3165	100,000 $\mu\text{S}/\text{cm}$	$\pm 0.25\%$ tolerance	1 quart
YSI 3167	1,000 $\mu\text{S}/\text{cm}$	$\pm 1.0\%$ tolerance	8 pints
YSI 3168	10,000 $\mu\text{S}/\text{cm}$	$\pm 1.0\%$ tolerance	8 pints
YSI 3169	50,000 $\mu\text{S}/\text{cm}$	$\pm 1.0\%$ tolerance	8 pints



Conductivity Cell Selection Chart for the 3200 (For the 3100 see specific ranges on back)

3200 Instrument Specifications				3100 Instrument Specifications		
Technology	Resistance Ratio			Forced Current		
Modes	Conductivity Resistivity Salinity Temperature	Conductance Resistance Total Dissolved Solids Conductance		Conductivity Salinity Conductance Temperature		
Conductance	Range	Accuracy	Resolution	Range (Conductivity)	Accuracy	Resolution
	0 to 0.9999 µS 0.950 to 9.999 µS 9.50 to 99.99 µS 95.0 to 999.9 µS 950 to 9999 µS 9.50 to 99.99 mS 95.0 to 999.9 mS 0.95 to 3.00 S	±0.30% full scale ±0.20% full scale ±0.10% full scale ±0.10% full scale ±0.10% full scale ±0.10% full scale ±0.30% full scale ±1.0% full scale	0.0001 µS 0.001 µS 0.01 µS 0.1 µS 1 µS 0.01 mS 0.1 mS 0.01 S	0 to 49.99 µS/cm <sup>1</sup> 0 to 499.9 µS/cm 0 to 4999 µS/cm 0 to 49.99 mS/cm <sup>2</sup> 0 to 499.9 mS/cm <sup>3</sup>	±0.50% full scale ±0.50% full scale ±0.50% full scale ±0.50% full scale ±0.50% full scale	0.01 µS/cm 0.1 µS/cm 1 µS/cm 0.01 mS/cm 0.1 mS/cm
Resistance	Range	Accuracy	Resolution			
	0 to 9.999 0 to 99.99 0 to 999.9 0 to 9.999 k 0 to 99.99 k 100.0 to 999.9 k 1.00 to 9.99 M 10.0 to 29.9 M	±0.2% full scale ±0.1% full scale ±0.1% full scale ±0.1% full scale ±0.1% full scale ±0.2% full scale ±0.5% full scale ±1% full scale	0.001 0.01 0.1 0.001 k 0.01 k 0.1 k 0.01 M 0.1 M			
Salinity	0 to 80 ppt (NaCl)	±0.1 ppt	0.1 ppt	0 to 80 ppt	2% or ±0.1 ppt	0.1 ppt
Temperature	-5 to +100°C	±0.1°C	0.01°C	-5 to +95°C	±0.1°C + 1 lsd	0.1°C
TDS	0 to 19,999 mg/L	±0.50%	1 mg/L			
Temperature Compensation						
Method	linear, nonlinear			linear		
Reference Temperature	0 to 100°C			15 to 25°C		
Temperature Coefficient	0 to 10%, nonlinear			0 to 4%		
Cell Configuration Storage	6 configurations			na		
Data Storage	100 points			na		
Cell Constant	0.001 to 100 cm <sup>-1</sup>			0.01, 0.1, 1, 10 cm <sup>-1</sup>		
Cell Calibration	up to 5 points			single point		
Output	RS232			na		
Alarm & Clock	yes			na		
Display	Graphic LCD			LCD		
Cell Connector	7-pin mini DIN			7-pin mini DIN		
Platinizing	included			included		
Power	115, 220 VAC			115, 220 VAC		
Approvals	UL, CSA, CE			UL, CSA, CE		
Environment	95% RH non-condensing			95% RH non-condensing		

1 - Do not use K = 10 cm<sup>-1</sup> cell.  
2 - Requires K = 10 cm<sup>-1</sup> or 1.0 cm<sup>-1</sup> cell  
3 - Requires K = 10 cm<sup>-1</sup> cell

### Cells with built-in temperature sensors

	cos	S.I.	Cell	Overall	Max	Chamber	Chamber		
Model	Cell Type	Cell Constant	Constant	Length	O.D.	I.D.	Depth	Volume	
A	3252 dip	1.0/cm	100/m	146 mm	13 mm	10 mm	20 mm		
B	3253 dip, micro	1.0/cm	100/m	178 mm	13 mm	10 mm	51 mm		
C	3254 fill	1.0/cm	100/m	135 mm	19 mm	11 mm	83 mm	5 mL	
D	3255 flow	0.1/cm	10/m	146 mm	25 mm	21 mm	76 mm	30 mL	
E	3256 dip	0.1/cm	10/m	159 mm	25 mm	21 mm	52 mm		

### Cells without built-in temperature sensors\*

	cos	S.I.	Cell	Overall	Max	Chamber	Chamber		
Model	Cell Type	Cell Constant	Constant	Length	O.D.	I.D.	Depth	Volume	
F	3401 dip	1.0/cm	100/m	191 mm	25 mm	21 mm	76 mm		
G	3402 dip	0.1/cm	10/m	159 mm	25 mm	21 mm	52 mm		
H	3403 dip	1.0/cm	100/m	178 mm	13 mm	10 mm	51 mm		
I	3417 dip	1.0/cm	100/m	146 mm	13 mm	10 mm	20 mm		
J	3418 dip	0.1/cm	10/m	159 mm	13 mm	10 mm	30 mm		
J	3440 dip	10/cm	1000/m	203 mm	13 mm	2 mm	86 mm		

\*Requires a YSI 3232 Cell Adaptor for use with YSI 3100 and 3200 Conductivity Instruments. For automatic temperature compensation, use a YSI 3220 on the 3200 or a temperature probe.

## YSI

1725 Brannum Lane, Yellow Springs, OH 45387  
Tel +1 937.767.7241 800.897.4151 (US)  
info@ysi.com  
YSI.com @YSIinc facebook.com/myYSI

YSI and Resistance Ratio Technology are registered trademarks.  
Specifications are subject to change. Please visit YSI.com to verify all specs.  
©2014 YSI, a Xylem brand  
■ Printed in the USA. W40-06 0714



a xylem brand