

Economical Oil Bath

BO400/410/500/601

Operating temp. range	Room temp.+10~180°C BO400/410	Room temp.+5~199°C BO500	Room temp.+5~180°C BO601
-----------------------	----------------------------------	-----------------------------	-----------------------------

Bath capacity	4L BO400/410	5.2L BO500	7L BO601
---------------	-----------------	---------------	-------------

Easy to use, digital setting, compact design oil bath



BO400/410



BO500 + MB800 (Magnetic Stirrer)



BO601

- Digital temperature setting by ▲/▼ keys
- Removable oil tank for convenient cleaning and changing of oil
- Heater situated outside the water tank
- Exclusive connection for bath operational setting function with RE601/801 rotary evaporator
- Stainless steel oil bath
- Bath protection sheet to prevent operator from burning
- Must be used with MB800 magnetic stirrer
- Digital temperature setting by ▲/▼ keys
- Protected oil tank prevents burns caused by contact
- Equipped with a drain

Specifications

Model		BO400		BO410	BO500	BO601
Operating temp. range* ¹		Room temp. +10~180°C			Room temp. +5~199°C	Room temp. +5~180°C
Temp. control accuracy* ²		±2°C (at agitation)			±0.5°C	±0.3°C (at 100°C)
Temp. control		PID control by microprocessor			Proportional control	PID control by microprocessor
Temp. setting / display		Digital setting by ▲/▼ keys			Digital / Glass thermometer	Digital setting by ▲/▼ keys
Operation function		Fixed temperature, Quick auto-stop, Auto stop, Auto start			--	Fixed temperature, Quick auto-stop, Auto stop, Auto start
Additional functions		Keypad lock, RE signal transmission and reception, Power failure recovery, Calibration off-set			--	Keypad lock, Power failure recovery, Calibration off-set
Heater		1kW(100V) 1.44kW(120V)		1kW(200V)1.44kW(240V)	Pipe heater 700W	SUS316 pipeheater 1kW
Sensor		K thermocouple			Pt100Ω	K thermocouple
Safety device		Bath protection cover (ABS heat-resistant resin)			Bath protection sheet	Bath protection cover
		Self-diagnostic function (Automatic overheat prevention, Temperature sensor error, Triac short circuit, Heater disconnection, Main relay failure), Circuit protector, Thermal fuse, Micro switch to detect heating without oil				Self-diagnostic function (Automatic overheat prevention, Temperature sensor error, Triac short circuit, heater disconnection, Main relay failure), Circuit protector, Thermal fuse
Interlocking control function		RE601/801 signal transmission and reception (Constant operation, Heat retention operation, Stop), Error report to RE601/801			--	--
Water tank	Capacity	Approx. 4L			Approx. 5.2L	Approx. 7L
	Dimensions	Max. I.D.240×bottom Dia165×D122mm			ø240×130mm	I.D.250×D150mm
External dimensions		W340×D349×H231mm			W250×D290×H130mm	W310×D360×H230mm
Weight		Approx. 5.5kg			Approx. 1.4kg	Approx. 8kg
Power source (50/60 Hz)		AC100~120V 12.5~10.5A		AC200~240V 6.5~5.5A	AC220V 7A with step-down transformer (no breaker* ³)	AC220V 7A

*1 No load operation of bath only. Maximum temperature varies by different circumstances and operational conditions.

*2 Measured under ambient temperature at 23°C±5°C, humidity of 65%RH±20%(No load).

*3 When combined with magnetic stirrer MB800, power source is from MB800 main unit outlet.

Model	MB800 (in combination with BO500)
Stirring plate	Material: Aluminum, dimension: W250xD270mm
Stirring capacity	100ml~10L
Rotation speed	70~1200rpm
Motor	AC motor, Electronic control
Overheat prevention	70~200°C
Sensor	Thermistor
Safety device	Current leakage breaker, Oil bath power shutdown overheat prevention device
Power source (50/60Hz)	AC220V with step-down transformer (MB800+BO500 combined with oil bath)
External dimensions	W250xD270xH150mm
Weight	Approx. 4.2kg
Accessories	Stirrer 40mm 1pc.