TIA-525 Optical/Electrical Converter

Manual





<u>Topic</u> <u>Page</u>

GENERAL INFORMATION

Introduction	.3
Specifications	
Unpacking and Inspection	5
Battery Replacement	5
Controls	5
Operational Considerations	. 6
Spectral Response	7
Typical Waveforms	.8
Warranty and Repair Information	. 9



INTRODUCTION

The TIA-525 Optical to Electrical Converter is a convenient battery-operated detector/amplifier combination that mounts directly on the input of an oscilloscope, digitizer, or other readout device. With a band width of DC to 125 MHz, it accurately provides an electrical replica of the optical signal presented to it. It is fully capable of driving a 50 ohm cable terminated in its characteristic load.

Two basic models of the unit exist; the TIA-525S, containing a silicon detector for use in the spectral region between 400 and 1000 nm, and the TIA-525 I which contains an Indium-Gallium-Arsenide detector and is responsive in the 900 to 1700 nm spectral region. Both units are equipped with an ST fiber optic connector. Custom versions are also available with unconnectorized detectors for free-space beams.

The TIA-525 has selectable transimpedances of 1.4 K Ω and 14 K Ω plus a post amplifier with selectable gains of 1 or 10. Thus the overall responsivity ranges from approximately 1, 000 V/W to 100, 000 V/W at the peak of the detector response curve. Interstage coupling may be switched from DC to AC to avoid saturation of the second stage in those cases where the signal of interest is combined with a relatively large DC optical component

Each unit is powered by a self-contained 9 V lithium battery or a universal wall mount power supply. Battery operation eliminates ground loops and the undesirable effects of conducted radiation that may be present on local power lines.

FEATURES AND BENEFITS

- Capability to drive 50 Ohm output loads
- Operates from Battery or Line Power
- DC to 125 MHz Analog Bandwidth
- Low Noise 3.0 pW/root-Hz
- Silicon or InGaAs detectors
- Selectable Gain Settings





Specifications					
Detector Type	Silicon or InGaAs (TIA-525S, TIA-525I respectively)				
Analog Signal Bandwidth (-3 dB)	DC to 125 MHz (Tr = 1.4 K), DC to 35 MHz (Tr = 14 K)				
Selectable Transimpedance settings	1.4 K Ohms, 14 K Ohms				
Second Stage Gain Selections	X 1 or X 10				
Maximum Linear Input Power	1.2 mW				
Maximum Input power without damage	10 mW				
Spectral Response	Silicon: 400 to 1000 nm, InGaAs: 850 - 1700 nm				
Output Impedance	50 Ohms				
Output Connector	Male BNC				
Fiber Optic Connector	Specify FC, ST or Free-Space				
Input Numerical Aperture	0.29				
Inter-stage Coupling	DC or AC (100 Hz Low Frequency Cutoff)				
Output Offset Voltage	+/- 0.1 Volt				
Noise Level	3.0 pW/ root-Hz at peak responsivity				
Maximum Output Voltage	4 V pk-pk, no load, 2 V pk-pk with 50 Ohm Load				
Power Requirements	Power Requirements 9 V Lithium Battery or supplied universal wal mount power supply				
Battery Life	Approximately 30 hours, (no load)				
Wall-mount Supply Power Requirements	95-260VAC, 50 - 60 Hz, 16 VA Max.				
Mains Connectors Supplied	North America, British, Continental Europe, Australian				
Dimensions (mm)	63 L x 30.5 W x 32 H				
Weight	5.6 oz (0.16 Kg)				
LED Annunciators Provided	Power On				
Operating Temperature Range	0 - 40 C				
Standard Warranty	Two Years, Component and Workmanship, 30 day Satisfaction Guarantee				
Accessories Supplied	Transit Case, Universal Power Supply, 9 V ULTRALIFE Lithium Battery, Manual on CD				



UNPACKING AND INSPECTION


Prior to shipment this instrument was inspected and found to be free of mechanical and electrical defects. Upon acceptance by the carrier he assumes responsibility for its safe arrival. After unpacking, examine the unit for any evidence of shipping damage. Should you receive this instrument in a damaged condition, apparent or concealed, it must be noted on the freight bill or express receipt and signed by the carrier's agent. Failure to do so could result in the carrier refusing to honor the claim. Upon filing a claim TREND Networks should be notified.

BATTERY REPLACEMENT

Each unit comes equipped with a 9 V Lithium battery that provides power to the unit for approximately 30 hours of operation. It is recommended that the battery be replaced whenever the output signal becomes clipped at 1 volt or less. When replacing the battery, a Lithium unit should be used. Conventional 9 V alkaline batteries may be used if so desired but the useful life will only be about 25% (8 hours) of that of the much higher capacity Lithium types. TREND Networks can supply these batteries if desired. Replacement of the battery may be accomplished by removing the four 2-56 Philips flat head screws that retain the bottom cover of the TIA-525. DO NOT attempt to remove the top cover. Take care to replace all screws tightly. This will provide optimum shielding of the unit from ambient radio frequency noise or interference.

The TIA-525 is also supplied with a universal power supply that operates from 90 to 240 VAC, 50-60 Hz. Each unit is equipped with four interchangeable power plugs that equip the unit for use in North America, Europe, the UK or Australia. Plugging the power supply into the unit disconnects the internal battery.

CONTROLS





OPERATIONAL CONSIDERATIONS

The TIA-500 is comprised of a fiber coupled detector and two amplifier stages. The first amplifier is a transimpedance stage which converts the detector output current to a voltage by passing it through a resistor of 1 400 or 14000 ohms. Additional amplification is optionally provided by the second stage which also serves to provide 50 ohm drive capability. Either AC or DC coupling between the stages may be selected.

The overall bandwidth of the unit is determined by the first stage transimpedance. It is in excess of 125 MHz when the TR switch is in the 1.4 K position and is 35 MHz in the 14 K position. The overall responsivity of the unit in terms of Volts/Watt is the current responsivity of the detector multiplied by the transimpedance and further multiplied by the second stage gain. For example, the sensitivity of the unit at a wavelength of 1300 nm would be 0.7 A/W x 1400 V/A x 10 = 10, 000V/W. It is evident that the same responsivity may be obtained by using a transimpedance of 14 K and a second stage gain of one. However, the first setting will provide a bandwidth of 125 MHz while the second will provide a bandwidth of 35 Mhz. Since the overall peak-to-peak output noise increases with bandwidth, it is desirable to use the higher transimpedance setting assuming that the signal of interest does not exceed 35 MHz.

The selection of AC interstage coupling is useful when the user needs to examine a small signal in the presence of a large DC optical component, (e.g. Baseband fiber optic video). This will preclude the last stage from saturating on the DC component. Otherwise, DC coupling should be employed.

When using the TIA-525 mounted on an oscilloscope, the scope may have its input set to either 50 or 1 Meg ohm input impedance. If driving a coaxial cable, the cable should have a 50 ohm characteristic impedance and be terminated with a 50 ohm load. Note that the signal amplitude will be reduced by a factor of two. Spectral Response

The following table summarizes the operation of the unit under various operating conditions.

Setting Signal	TR	AC/DC Coupling	2nd Stage
Small Signal on large DC Components	1.4K	AC	X1, X10 As Needed
High Frequency signal, >35 MHz	1.4K	DC	X1, X10 As Needed
Low Level Signal<35 MHz	14K	DC	X1, X10 As Needed
Low Level, High Frequency Signal	1.4K	DC	X10





SPECTRAL RESPONSE

The approximate relative response curves of the detectors employed is as shown below. Note that these are representative curves and do not necessarily correspond to the exact response of the particular detector in use.

The approximate power at the detector surface is given by:

Input power in watts (InGaAs) =
$$\frac{\text{Peak output voltage (no load)}}{\text{0.8 A/W x T}_{R} \text{ x % Relative response from graph/100}}$$
Input power in watts (Si) =
$$\frac{\text{Peak output voltage (no load)}}{\text{0.55 A/W x T}_{R} \text{ x % Relative response from graph/100}}$$









Typical Waveforms


Optical Input




Output; $T_R = 1.4 \text{ K, Gain} = 1$




Optical Input




Output; $T_R = 14 \text{ K, Gain} = 1$



Optical Input



Output; $T_R = 1.4 \text{ K, Gain} = 10$





WARRANTY AND REPAIR INFORMATION

REPAIR INFORMATION

Products manufactured by TREND Networks are designed and manufactured to provide reliable performance. However, in the event that service is required, both telephone technical assistance and factory repair services are available. Call (973) 957-7700, e-mail contactus@trend-networks.com or visit our web site at https://www.trend-networks.com/us/ for more information or to request an RMA number.

For IN-WARRANTY REPAIRS, call us to obtain a Returned Material Authorization number, (RMA Number). All products are to be returned to TREND Networks with freight charges pre-paid. Those products sent under warranty will be returned to our customers pre-paid. We cannot be responsible for returned products that do not reference the TREND Networks RMA number.

For OUT-OF-WARRANTY repairs, services are billable for both time and materials.

LIMITED WARRANTY

TREND NETWORKS WARRANTS THAT TO THE FIRST PURCHASER, FOR A PERIOD OF TWO YEARS FROM THE DATE OF RECEIPT, THAT THIS PRODUCT (THE PRODUCT) WILL BE FREE FROM DEFECTS IN MATERIALS AND MANUFACTURING. THE FOREGOING WARRANTY IS THE ONLY WARRANTY, EXPRESS OR IMPLIED, GIVEN BY TREND NETWORKS, I.E., THERE IS NO WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE. TREND NETWORKS HEREBY DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY OTHER THAN THE WARRANTY IN THE FIRST SENTENCE TO THE FULLEST EXTENT PERMITTED BY LAW.

THE SOLE AND EXCLUSIVE REMEDY UNDER THIS WARRANTY IS REPAIR OR REPLACEMENT AT TREND NETWORKS' OPTION OF ANY PRODUCT THAT PROVES TO BE DEFECTIVE IN MATERIALS OR MANUFACTURING WITHIN TWO YEARS OF RECEIPT OF THE PRODUCT. NOTE: THIS WARRANTY DOES NOT APPLY TO ANY PRODUCT WHICH HAS BEEN SUBJECT TO MISHANDLING, MISUSE, OR SERVICE BY UNAUTHORIZED PERSONNEL OR TO ANY PRODUCT WHICH HAS BEEN DAMAGED, MODIFIED, ALTERED OR TAMPERED WITH.

TO THE FULLEST EXTENT OF THE LAW, TREND NETWORKS DISCLAIMS ALL LIABILITY FOR ANY OTHER DIRECT, INCIDENTAL OR CONSEQUENTIAL DAMAGES ALLEGED TO BE CAUSED BY A DEFECTIVE PRODUCT, I.E., TREND NETWORKS WILL NOT BE RESPONSIBLE FOR ANY PERSONAL INJURY, PROPERTY DAMAGE OTHER THAN THE COST OF REPLACING THE PRODUCT OR ANY OTHER MONETARY DAMAGE SUCH AS LOST WAGES OR PROFITS CAUSED BY ANY USE, ATTEMPTED USE OR INABILITY TO USE THE PRODUCT. NOTE: BY USING THE PRODUCT, YOU AGREE THAT REPAIR OR REPLACEMENT AT TREND NETWORKS' OPTION WILL FULLY SATISFY TREND NETWORKS WARRANTY OBLIGATION TO YOU, WHETHER IN CONTRACT, TORT, NEGLIGENCE, STRICT LIABILITY OR OTHER APPLICABLE LAW.



TREND NETWORKS North America 300 Roundhill Drive, Suite 1, Rockaway, NJ 07866, USA Tel. 973-957-7700

contactus@trend-networks.com

www.trend-networks.com



Specification subject to change without notice. E&OE © TREND NETWORKS 2022