

Always check the website for the most updated specifications: www.americh.com



Tub pictured with optional waste & overflow.


35 32 0






All bathtub dimensions are $\pm 1/2$ ".


Builder Series




Luxury Series




Platinum Series Combination





(pump and blower location only)



Airbath System III Airbath System III







INSTALLATION TIPS

- Install according to Owner's Manual and local codes.
- Airbath III units may be 11/2" 21/2" higher than stated.
- Any whirlpool or Airbath® unit requires an access panel.
- Hot water supply should be 65-75% of tub capacity or greater.
- Always consult your local plumber for recommendations as installations will vary.
- Cut-out dimensions: 58" x 38"

DIMENSIONS

60" x 40" x 33" ($1524 \times 1016 \times 838 \text{ mm}$) Whirlpool Operating Gallons = 85 (Liters = 322) Gallon to Overflow = 135 (Liters = 511)

MATERIAL: Acrylic (All Americh Standard Colors)

TUB FLOOR: Textured

UNDERMOUNT: Yes

- Advise Americh when ordering to ensure there are no issues with deck mounted controls.
- Always take dimensions directly from the unit.

ELECTRICAL REQUIREMENTS

Americh recommends one 20 amp ground fault circuit interrupter (GFCI) for each power supply provided with the bathtub.

OPTIONAL ACCESSORIES

- Chromatherapy*
- Grab Bars: 9" 14"* 16"
- High Density Insulation*
- iBath Sound System
- Inline Heater (whirlpool only)
- Jets: Additional or Rotary*
- Lo Profile Tub Edge
- Ozone System (whirlpool and/or Airbath only)
- Pillow: 13"*

Angle - Full Back

- Remote Control Upgrade (select series only)
- Serenity Soak (tub only)
- Syllent Pump with Heated Air*
- Tile Flange Kit
- Trim Kit Upgrade*
- Waste & Overflow
 - Cable Drive Overflow*
 - Linear Overflow

CODES AND COMPLIANCE

Americh products meet or exceed the following standards:

- Underwriters Laboratories (UL)
- Underwriters Laboratories Canada (cUL)
- Canadian Standards Association (CSA)
- ANSI Z124.1 ANSI A112-19.7
- ANSI A112.19.8 ASTM F462-79

Contact Americh for additional approvals.

^{*}Standard on Platinum Series