

SAFETY LIGHT CURTAINS



SAFETY LIGHT CURTAINS



Ordering information

C4000 Palletizer Advanced without extension connection

Illustration may differ

| Resolution | Scanning range | Protective field height | System part | Туре | Part no. |
|------------|-------------------|----------------------------|-------------|--------------------|----------|
| 30 mm | 7 m | 1,800 mm | Receiver | C40E- 1803FK010 | 1043162 |

Other models and accessories → www.sick.com/C4000_Palletizer



Detailed technical data

| Features | | |
|--|--|--|
| Description | C4000 Palletizer Advanced without extension connection | |
| Application | Normal industrial environment | |
| System part | Receiver | |
| Resolution | 30 mm | |
| Scanning range | 7 m | |
| Protective field height | 1,800 mm | |
| Synchronization | Optical synchronisation | |
| Items supplied | Receiver | |
| Safety-related parameters | | |
| Туре | Type 4 (IEC 61496-1) | |
| Safety integrity level | SIL 3 (IEC 61508) | |
| Category | Category 4 (EN ISO 13849) | |
| Performance level | PL e (EN ISO 13849) | |
| $\ensuremath{PFH}_{\ensuremath{D}}$ (mean probability of a dangerous failure per hour) | 15 * 10 ⁻⁹ | |
| T _M (mission time) | 20 years (EN ISO 13849) | |
| Safe state in the event of a fault | At least one OSSD is in the OFF state. | |

Functions

| | Functions | Delivery status |
|--|-----------|-----------------|
| Function range | Advanced | |
| Protective operation | 1 | |
| Restart interlock | 1 | Internal |
| External device monitoring (EDM) | 1 | Deactivated |
| Beam coding | 1 | Code 1 |
| Configurable scanning range | 1 | 0.5 m 7 m |
| Reduced resolution | 1 | 2 beams |
| Self-teaching dynamic blanking for goods detection | ✓ | |

SAFETY LIGHT CURTAINS

| | Functions | Delivery status |
|---|-----------|-----------------|
| Self-teaching dynamic blanking for pallet detection | ✓ | |
| Multiple sampling | 1 | 2x evaluation |
| Direction monitoring | 1 | |
| Object entry monitoring | 1 | |
| Safe SICK device communication via EFI | ✓ | |

Functions in combination with UE402

| Bypass | 1 |
|--------------------------|---|
| Operating mode switching | ✓ |

Interfaces

| System connection | Hirschmann male connector M26, 12-pin |
|-------------------------------|---|
| Direction of cable connection | Straight |
| Conductor cross section | 0.75 mm ² |
| Permitted cable length | ≤ 50 m ¹⁾ |
| Configuration connection | Female connector M8, 4-pin |
| Configuration method | PC with CDS (Configuration and Diagnostic Software) |
| Display elements | 7-segment display |

 $^{(1)}$ Depending on load, power supply and wire cross-section. The technical specifications must be observed.

Electrical data

| Protection class | III (IEC 61140) |
|---|--|
| Supply voltage V _S | 24 V DC (19.2 V 28.8 V) ¹⁾ |
| Residual ripple | < 10 % ²⁾ |
| Output signal switching devices (OSSDs) | |
| Type of output | 2 PNP semiconductors, short-circuit protected, cross-circuit monitored ³⁾ |
| ON state, switching voltage HIGH | 24 V DC (V_S – 2.25 V DC V_S) |
| OFF state, switching voltage LOW | ≤ 2 V DC |
| Current-carrying capacity per OSSD | ≤ 500 mA |
| Application diagnostic output (ADO) | |
| Output voltage HIGH (active) | 24 V DC (15 V DC 28.8 V DC) |
| Output voltage LOW (deactivated) | High resistance |
| Output current HIGH (active) | ≤ 100 mA |

¹⁾ The external voltage supply must be capable of buffering brief mains voltage failures of 20 ms as specified in EN 60204-1. Suitable power supplies are available as accessories from SICK.

 $^{2)}$ Within the limits of $\mathrm{V}_{\mathrm{S}}.$

 $^{3)}$ Applies to the voltage range between –30 V and +30 V.

Mechanical data

| Dimensions | See dimensional drawing |
|-----------------------|---------------------------|
| Housing cross-section | 48 mm x 40 mm |
| Housing material | Aluminum extruded profile |
| Weight | 3,710 g |

SAFETY LIGHT CURTAINS

Ambient data

| Enclosure rating | IP65 (EN 60529) |
|-------------------------------|---------------------------------|
| Ambient operating temperature | 0 °C +55 °C |
| Storage temperature | -25 °C +70 °C |
| Air humidity | 15 % 95 %, Non-condensing |
| Vibration resistance | 5 g, 10 Hz 55 Hz (EN 60068-2-6) |
| Shock resistance | 10 g, 16 ms (EN 60068-2-27) |

850 nm

Other information


Wave length


Classifications

| ECLASS 5.0 | 27272704 |
|----------------|----------|
| ECLASS 5.1.4 | 27272704 |
| ECLASS 6.0 | 27272704 |
| ECLASS 6.2 | 27272704 |
| ECLASS 7.0 | 27272704 |
| ECLASS 8.0 | 27272704 |
| ECLASS 8.1 | 27272704 |
| ECLASS 9.0 | 27272704 |
| ECLASS 10.0 | 27272704 |
| ECLASS 11.0 | 27272704 |
| ECLASS 12.0 | 27272704 |
| ETIM 5.0 | EC002549 |
| ETIM 6.0 | EC002549 |
| ETIM 7.0 | EC002549 |
| ETIM 8.0 | EC002549 |
| UNSPSC 16.0901 | 46171620 |

SAFETY LIGHT CURTAINS

Dimensional drawing (Dimensions in mm (inch))






♦

∢

₿

74 (2.91)



Cable sockets M26 x 11 + FE with crimp contacts

Illustration sender (receiver mirror image)

| | L1 | L2 | Α |
|-------|-------|-------|-------|
| 300 | 381 | 427 | 224 |
| 450 | 532 | 578 | 374 |
| 600 | 682 | 728 | 524 |
| 750 | 833 | 879 | 674 |
| 900 | 984 | 1.030 | 824 |
| 1.050 | 1.134 | 1.180 | 974 |
| 1.200 | 1.283 | 1.329 | 1.124 |
| 1.350 | 1.435 | 1.481 | 1.274 |
| 1.500 | 1.586 | 1.632 | 1.424 |
| 1.650 | 1.736 | 1.782 | 1.574 |
| 1.800 | 1.887 | 1.933 | 1.724 |

SAFETY LIGHT CURTAINS

Recommended accessories

Other models and accessories -> www.sick.com/C4000_Palletizer

| | Brief description | Туре | Part no. | |
|---------------------------------|---|------------------------------|----------|--|
| Alignment ai | ids | | | |
| Ŵ | Laser alignment aid for various sensors, laser class 2 (IEC 60825). Do not look into the beam!, 19 mm x 67.3 mm x 66.9 mm | AR60 | 1015741 | |
| | Adapter AR60 for housing cross-section 48 mm x 40 mm | AR60 adapter, 48x40 | 4032461 | |
| | Adapter AR60 for housing cross-section 48 mm x 40 mm in PU3H device column | AR60 adapter, 48x40, PU3H | 4056731 | |
| Optics cloths | 5 | | | |
| SICK | Cloth for cleaning optical surfaces | Lens cloth | 4003353 | |
| Test and mo | nitoring tools | | | |
| | 30 mm diameter, 250 mm length | Test rod 30 mm | 2022602 | |
| Mounting br | ackets and plates | | | |
| | 4 pieces, Mounting kit 1, mounting bracket, rigid, L-shaped, including fixing screws and washers | BEF-3WNGBAST4 | 7021352 | |
| Plug connec | tors and cables | | | |
| | Connection type head A: Female connector, M26, 12-pin, straight Description: Unshielded Connection systems: Crimp contacts Permitted cross-section: 0.5 mm² 1.5 mm² Note: 12 crimping contacts enclosed | DOS-0612G000GA3KM0 | 6020757 | |
| 6 | Connection type head A: Female connector, M26, 12-pin, angled Description: Unshielded Connection systems: Crimp contacts Permitted cross-section: 0.5 mm² 1.5 mm² Note: 12 crimping contacts enclosed | DOS-0612W000GA3KM0 | 6020758 | |
| | Connection type head A: Male connector, M26, 12-pin, straight Description: Unshielded Connection systems: Crimp contacts Permitted cross-section: 0.5 mm² 1.5 mm² Note: 12 crimping contacts enclosed | STE-0612G000GA3KM0 | 6021191 | |
| | Connection type head A: Male connector, M26, 12-pin, angled Description: Unshielded Connection systems: Crimp contacts Permitted cross-section: 0.5 mm² 1.5 mm² Note: 12 crimping contacts enclosed | STE-0612W000GA3KM0 | 6021192 | |
| Terminal and alignment brackets | | | | |
| | 4 pieces, Mounting kit 6, side bracket, rotatable, zinc diecast | BEF-1SHABAZN4 | 2019506 | |
| 9 | 4 pieces, Omega bracket, rotatable, fixable with only one screw, for mounting on the swivel mount | BEF-2SMMEAAL4 | 2044847 | |

SAFETY LIGHT CURTAINS

| | Brief description | Туре | Part no. |
|----------------------|---|--------------------|----------|
| | 4 pieces, Mounting kit 2, rotatable, swivel mount, Polyamide PA6 | BEF-2SMMEAKU4 | 2019659 |
| Others | | | |
| | Connection type head A: Male connector, M8, 4-pin, straight Connection type head B: Male connector, USB-A, straight Cable: 2 m, 4-wire, PVC Description: Unshielded, Configuration cable with integrated RS-232 transducer on USB for connecting a sensor configuration connection (M8, 4-pin) to the USB interface of a PC | DSL-8U04G02M025KM1 | 6034574 |
| | Connection type head A: Male connector, M8, 4-pin, straight Connection type head B: Male connector, USB-A, straight Cable: 10 m, 4-wire, PVC Description: Unshielded, Configuration cable with integrated RS-232 transducer on USB for connecting a sensor configuration connection (M8, 4-pin) to the USB interface of a PC | DSL-8U04G10M025KM1 | 6034575 |
| 16 | Connection type head A: Female connector, M26, 12-pin, straight Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 20 m, 12-wire, PVC Description: Sensor/actuator cable, unshielded Connection systems: Flying leads | DOL-0612G20M075KM0 | 2022549 |
| 10 | Connection type head A: Female connector, M26, 12-pin, straight Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 15 m, 12-wire, PVC Description: Sensor/actuator cable, unshielded Connection systems: Flying leads | DOL-0612G15M075KM0 | 2022548 |
| N. | Connection type head A: Female connector, M26, 12-pin, straight Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 10 m, 12-wire, PVC Description: Sensor/actuator cable, unshielded Connection systems: Flying leads | DOL-0612G10M075KM0 | 2022547 |
| N. | Connection type head A: Female connector, M26, 12-pin, straight Connection type head B: Flying leads Cable: 5 m, PVC Description: Unshielded Connection systems: Flying leads Note: Without EFI: Pin 9 and 10 not connected | DOL-0610G05M075KM1 | 2046888 |
| 10 | Connection type head A: Female connector, M26, 12-pin, straight Connection type head B: Flying leads Cable: 10 m, PVC Description: Unshielded Connection systems: Flying leads Note: Without EFI: Pin 9 and 10 not connected | DOL-0610G10M075KM1 | 2046889 |
| N. | Connection type head A: Female connector, M26, 12-pin, straight Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 12-wire, PVC Description: Sensor/actuator cable, unshielded Connection systems: Flying leads | DOL-0612G05M075KM0 | 2022545 |
| Switching amplifiers | | | |
| • | Applications: Functionality upgrade Compatible sensor types: C4000 safety light curtains Description: Upgrades the C4000 Standard, Advanced, Palletizer, Entry/Exit, and Fusion to include the functions defined in the technical specifications, e.g., bypass, operating mode switching, and PSDI in the case of C4000 Standard, Advanced. | UE402 | 1023577 |

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

