

Job or Customer :	
Location :	
Engineer :	
☐ Complies with Spec ☐ Alternate	Notes :
Contractor :	
HeatLink Rep :	
Submitted By :	Date :
Approved By :	Date :
P.O. Number :	Date :

Description

Solid no lead brass PEX insert tees.

Listings

cNSFus-pw

Standards

ASTM F877
ASTM F1807
CSA B137.5
NSF/ANSI 14
NSF/ANSI 61
NSF/ANSI 372


Technical Data

Material:..... No Lead (Eco) Brass - C69300
Operating Pressure Rating:..... 180°F @ 100 psi (82.2°C @ 0.69 MPa)

Codes

IAPMO UPC

Dimensional Diagram



Installation

Installation must follow all of HeatLink's instructions and guidelines.


Related Documents

- HeatLink Limited Plumbing Warranty

PEX Insert Tees

Qty	Stk. #	Size (run × run × branch)	Dimension, in / (mm)							ID 1	ID 2	ID 3	Weight, lb / (kg)
			A	B	C	D	E	F	G				
	26555NL	½" × ½" × ½" PEX	0.63 (16.0)	0.35 (9.0)	0.35 (9.0)	0.63 (16.0)	0.28 (7.0)	0.35 (9.0)	0.63 (16.0)	0.35 (8.9)	0.35 (8.9)	0.35 (8.9)	0.060 (0.027)
	26222NL	¾" × ¾" × ¾" PEX	0.63 (16.0)	0.43 (11.0)	0.43 (11.0)	0.63 (16.0)	0.37 (9.5)	0.43 (11.0)	0.63 (16.0)	0.53 (13.5)	0.53 (13.5)	0.53 (13.5)	0.100 (0.046)
	26888NL	1" × 1" × 1" PEX	0.81 (20.5)	0.53 (13.5)	0.53 (13.5)	0.81 (20.5)	0.47 (12.0)	0.53 (13.5)	0.81 (20.5)	0.71 (18.0)	0.71 (18.0)	0.71 (18.0)	0.185 (0.084)
	26333NL	1 ¼" × 1 ¼" × 1 ¼" PEX	0.94 (24.0)	0.75 (19.1)	0.75 (19.1)	0.94 (24.0)	0.56 (14.3)	0.75 (19.1)	0.94 (24.0)	0.87 (22.1)	0.87 (22.1)	0.87 (22.1)	0.370 (0.168)
	26444NL	1 ½" × 1 ½" × 1 ½" PEX	1.15 (29.2)	0.88 (22.3)	0.88 (22.3)	1.15 (29.2)	0.65 (16.5)	0.89 (22.5)	1.15 (29.2)	1.04 (26.5)	1.04 (26.5)	1.04 (26.5)	0.531 (0.241)
	26666NL	2" × 2" × 2" PEX	1.50 (38.1)	1.10 (28.0)	1.10 (28.0)	1.50 (38.1)	0.85 (21.5)	1.10 (28.0)	1.50 (38.1)	1.37 (34.7)	1.37 (34.7)	1.37 (34.7)	1.021 (0.463)


Dimensional Diagram



PEX Insert Reducing Tees

Qty	Stk. #	Size (run × run × branch)	Dimension, in / (mm)							ID 1	ID 2	ID 3	Weight, lb / (kg)
	26552NL	½" × ½" × ¼" PEX	0.63 (16.0)	0.43 (11.0)	0.43 (11.0)	0.63 (16.0)	0.37 (9.5)	0.43 (11.0)	0.63 (16.0)	0.35 (8.9)	0.35 (8.9)	0.53 (13.5)	0.112 (0.051)
	26255NL	¾" × ½" × ½" PEX	0.63 (16.0)	0.43 (11.0)	0.43 (11.0)	0.63 (16.0)	0.37 (9.5)	0.43 (11.0)	0.63 (16.0)	0.53 (13.5)	0.35 (8.9)	0.35 (8.9)	0.101 (0.046)
	26252NL	¾" × ½" × ¾" PEX	0.63 (16.0)	0.43 (11.0)	0.43 (11.0)	0.63 (16.0)	0.37 (9.5)	0.43 (11.0)	0.63 (16.0)	0.53 (13.5)	0.35 (8.9)	0.53 (13.5)	0.099 (0.045)
	26225NL	¾" × ¾" × ½" PEX	0.63 (16.0)	0.43 (11.0)	0.43 (11.0)	0.63 (16.0)	0.37 (9.5)	0.43 (11.0)	0.63 (16.0)	0.53 (13.5)	0.53 (13.5)	0.35 (8.9)	0.100 (0.046)
	26822NL	1" × ¾" × ¾" PEX	0.81 (20.5)	0.53 (13.5)	0.53 (13.5)	0.63 (16.0)	0.47 (12.0)	0.53 (13.5)	0.63 (16.0)	0.71 (18.0)	0.53 (13.5)	0.53 (13.5)	0.172 (0.078)
	26885NL	1" × 1" × ½" PEX	0.81 (20.5)	0.41 (10.5)	0.41 (10.5)	0.81 (20.5)	0.47 (12.0)	0.59 (15.0)	0.63 (16.0)	0.71 (18.0)	0.71 (18.0)	0.35 (8.9)	0.154 (0.070)
	26882NL	1" × 1" × ¾" PEX	0.81 (20.5)	0.53 (13.5)	0.53 (13.5)	0.81 (20.5)	0.47 (12.0)	0.53 (13.5)	0.63 (16.0)	0.71 (18.0)	0.71 (18.0)	0.53 (13.5)	0.176 (0.080)
	26322NL	1 ¼" × ¾" × ¾" PEX	0.94 (24.0)	0.43 (11.0)	0.43 (11.0)	0.63 (16.0)	0.56 (14.3)	0.75 (19.1)	0.63 (16.0)	0.87 (22.1)	0.53 (13.5)	0.53 (13.5)	0.212 (0.096)
	26382NL	1 ¼" × 1" × ¾" PEX	0.94 (24.0)	0.50 (12.7)	0.50 (12.7)	0.81 (20.5)	0.56 (14.3)	0.75 (19.1)	0.63 (16.0)	0.87 (22.1)	0.71 (18.0)	0.53 (13.5)	0.243 (0.110)
	26388NL	1 ¼" × 1" × 1" PEX	0.94 (24.0)	0.53 (13.5)	0.53 (13.5)	0.81 (20.5)	0.56 (14.3)	0.75 (19.1)	0.81 (20.5)	0.87 (22.1)	0.71 (18.0)	0.71 (18.0)	0.269 (0.122)
	26335NL	1 ¼" × 1 ¼" × ½" PEX	0.94 (24.0)	0.43 (11.0)	0.43 (11.0)	0.94 (24.0)	0.56 (14.3)	0.75 (19.1)	0.63 (16.0)	0.87 (22.1)	0.87 (22.1)	0.35 (8.9)	0.353 (0.160)
	26332NL	1 ¼" × 1 ¼" × ¾" PEX	0.94 (24.0)	0.50 (12.7)	0.50 (12.7)	0.94 (24.0)	0.56 (14.3)	0.75 (19.1)	0.63 (16.0)	0.87 (22.1)	0.87 (22.1)	0.53 (13.5)	0.276 (0.125)
	26338NL	1 ¼" × 1 ¼" × 1" PEX	0.94 (24.0)	0.63 (16.0)	0.63 (16.0)	0.94 (24.0)	0.56 (14.3)	0.75 (19.1)	0.81 (20.5)	0.87 (22.1)	0.87 (22.1)	0.71 (18.0)	0.289 (0.131)

Dimensional Diagram



PEX Insert Reducing Tees

Qty	Stk. #	Size (run × run × branch)	Dimension, in / (mm)							ID 1	ID 2	ID 3	Weight, lb / (kg)
	26422NL	1 ½" × ¾" × ¾" PEX	1.15 (29.2)	0.45 (11.4)	0.45 (11.4)	0.63 (16.0)	0.65 (16.5)	0.89 (22.5)	0.63 (16.0)	1.04 (26.5)	0.53 (13.5)	0.53 (13.5)	0.275 (0.125)
	26488NL	1 ½" × 1" × 1" PEX	1.15 (29.2)	0.58 (14.7)	0.58 (14.7)	0.81 (20.5)	0.65 (16.5)	0.89 (22.5)	0.81 (20.5)	1.04 (26.5)	0.71 (18.0)	0.71 (18.0)	0.345 (0.157)
	26432NL	1 ½" × 1 ¼" × ¾" PEX	1.15 (29.2)	0.49 (12.4)	0.49 (12.4)	0.94 (24.0)	0.65 (16.5)	0.89 (22.5)	0.63 (16.0)	1.04 (26.5)	0.87 (22.1)	0.53 (13.5)	0.296 (0.134)
	26438NL	1 ½" × 1 ¼" × 1" PEX	1.15 (29.2)	0.58 (14.7)	0.58 (14.7)	0.94 (24.0)	0.65 (16.5)	0.89 (22.5)	0.81 (20.5)	1.04 (26.5)	0.87 (22.1)	0.71 (18.0)	0.364 (0.165)
	26433NL	1 ½" × 1 ¼" × 1 ¼" PEX	1.15 (29.2)	0.75 (19.1)	0.75 (19.1)	0.94 (24.0)	0.65 (16.5)	0.87 (22.2)	0.94 (24.0)	1.04 (26.5)	0.87 (22.1)	0.87 (22.1)	0.420 (0.190)
	26442NL	1 ½" × 1 ½" × ¾" PEX	1.15 (29.2)	0.44 (11.3)	0.44 (11.3)	1.15 (29.2)	0.65 (16.5)	0.89 (22.5)	0.63 (16.0)	1.04 (26.5)	1.04 (26.5)	0.53 (13.5)	0.323 (0.147)
	26448NL	1 ½" × 1 ½" × 1" PEX	1.15 (29.2)	0.58 (14.8)	0.58 (14.8)	1.15 (29.2)	0.65 (16.5)	0.89 (22.5)	0.81 (20.5)	1.04 (26.5)	1.04 (26.5)	0.71 (18.0)	0.410 (0.186)
	26443NL	1 ½" × 1 ½" × 1 ¼" PEX	1.15 (29.2)	0.76 (19.3)	0.76 (19.3)	1.15 (29.2)	0.65 (16.5)	0.89 (22.5)	0.94 (24.0)	1.04 (26.5)	1.04 (26.5)	0.87 (22.1)	0.452 (0.205)
	26633NL	2" × 1 ¼" × 1 ¼" PEX	1.50 (38.1)	0.77 (19.5)	0.77 (19.5)	0.94 (24.0)	0.85 (21.5)	1.10 (28.0)	0.94 (24.0)	1.37 (34.7)	0.87 (22.1)	0.87 (22.1)	0.683 (0.310)
	26642NL	2" × 1 ½" × ¾" PEX	1.50 (38.1)	0.49 (12.5)	0.49 (12.5)	1.15 (29.2)	0.85 (21.5)	0.98 (25.0)	0.63 (16.0)	1.37 (34.7)	1.04 (26.5)	0.53 (13.5)	0.531 (0.241)
	26648NL	2" × 1 ½" × 1" PEX	1.50 (38.1)	0.77 (19.5)	0.77 (19.5)	1.15 (29.2)	0.85 (21.5)	1.10 (28.0)	0.81 (20.5)	1.37 (34.7)	1.04 (26.5)	0.71 (18.0)	0.694 (0.315)
	26643NL	2" × 1 ½" × 1 ¼" PEX	1.50 (38.1)	0.77 (19.5)	0.77 (19.5)	1.15 (29.2)	0.85 (21.5)	1.10 (28.0)	0.94 (24.0)	1.37 (34.7)	1.04 (26.5)	0.87 (22.1)	0.699 (0.317)
	26644NL	2" × 1 ½" × 1 ½" PEX	1.50 (38.1)	0.91 (23.0)	0.91 (23.0)	1.15 (29.2)	0.85 (21.5)	0.91 (23.0)	1.15 (29.2)	1.37 (34.7)	1.04 (26.5)	1.04 (26.5)	0.522 (0.237)
	26662NL	2" × 2" × ¾" PEX	1.50 (38.1)	0.49 (12.5)	0.49 (12.5)	1.50 (38.1)	0.85 (21.5)	0.98 (25.0)	0.63 (16.0)	1.37 (34.7)	1.37 (34.7)	0.53 (13.5)	0.584 (0.265)
	26668NL	2" × 2" × 1" PEX	1.50 (38.1)	0.57 (14.5)	0.57 (14.5)	1.50 (38.1)	0.85 (21.5)	1.10 (28.0)	0.81 (20.5)	1.37 (34.7)	1.37 (34.7)	0.71 (18.0)	0.657 (0.298)
	26663NL	2" × 2" × 1 ¼" PEX	1.50 (38.1)	0.77 (19.5)	0.77 (19.5)	1.50 (38.1)	0.85 (21.5)	1.10 (28.0)	0.94 (24.0)	1.37 (34.7)	1.37 (34.7)	0.87 (22.1)	0.756 (0.343)
	26664NL	2" × 2" × 1 ½" PEX	1.50 (38.1)	0.91 (23.0)	0.91 (23.0)	1.50 (38.1)	0.85 (21.5)	0.91 (23.0)	1.15 (29.2)	1.37 (34.7)	1.37 (34.7)	1.04 (26.5)	0.805 (0.365)

This page is intentionally blank.