Foam inserts for roller cabinet



ROLL-O



- High-quality, durable foam insert without chemical vapours
- Screwdriver with insulated blades for safe working up to 1,000 volt, five of which with reduced blade diameter for lower-lying screws
- Optimum fit for the best possible removal of the tools from the foam insert
- · Water- and oil-repellent, low maintenance and easy to clean
- Protection of the tool from dirt and impact
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer
- Take it easy tool finder: colour coding according to profile and size
- Hexagonal anti-roll feature against rolling away


Durable foam insert; two-coloured for quick identification of missing parts; suitable for the Tool Rebel roller cabinet, equipped with 14 Wera Kraftform VDE screwdrivers as well as two screw grippers.

9711 Foam insert VDE screwdriver set 1, 16 pieces

Foam inserts for roller cabinet



Safe storage and quick overview




The tools sit securely in the foam thanks to precise contour cutouts, but are easy to remove. The carefully designed arrangement of the tools ensures space-saving storage and quick access to each tool.

Lasertip



A precisely-focused laser creates a sharp-edged surface structure. Wera Lasertip "bites" itself into the screw head and prevents any slips out of the recess. It is available for screwdrivers for slotted, Phillips and Pozidriv screws.

Two-coloured foam insert



After removing the tool the light grey second foam becomes visible and therefore missing tools are quickly identified.

Individually tested tool as per IEC 60900 at 10,000V




The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.

And this is how the gripper

works

VDE-insulated screwdriver with reduced blade diameter



Reduced blade diameter with integrated protective insulation, allows sunken screws and spring elements to be accessed and actuated, individually tested as per IEC 60900.

And this is how the gripper works



Pull the screw gripper towards the screwdriver handle until the two arms of the gripper sit against the head of the screw and are spread slightly apart. The Wera screw gripper releases the screw automatically after it has been fastened.

"Take it easy" Tool Finder



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.



of the screwdriver until the end of the blade protrudes from the rubber blade holder.

9711 Foam insert VDE screwdriver set 1, 16 pieces

Foam inserts for roller cabinet



Set contents:

1x 1x 1x 1x 1x 1x 1x 1x 1x 1x 1x 1x 1x 1	liameter for Phillips screws, PH 1 x 80 mm PH 1 x 80 mm PH 2 x 100 mm liameter for Pozidriv screws, PZ 1 x 80 mm PZ 1 x 80 mm PZ 2 x 100 mm rs (Pozidriv/slotted), # 2 x 100 mm # 2 x 100 mm vs (Pozidriv/slotted), # 2 x 100 mm # 2 x 100 mm 0.4 x 2.5 x 80 mm 0.8 x 4 x 100 mm 1 x 5.5 x 125 mm neter for slotted screws, 0.6 x 3.5 x 100 mm 0.6 x 3.5 x 100 mm
1x de d 1x 1x 1x 1x 1x 1x 1x 1x 1x 1x	PH 2 x 100 mm liameter for Pozidriv screws, PZ 1 x 80 mm PZ 1 x 80 mm PZ 2 x 100 mm rs (Pozidriv/slotted), # 2 x 100 mm # 2 x 100 mm 2.5 x 80 mm 0.4 x 2.5 x 80 mm 0.4 x 2.5 x 80 mm 1 x 5.5 x 125 mm meter for slotted screws, 0.6 x 3.5 x 100 mm
de d 1x 1x 1x 1x 1x 1x 1x 1x 1x 1x 1x 1x	liameter for Pozidriv screws, PZ 1 x 80 mm PZ 1 x 80 mm PZ 2 x 100 mm rs (Pozidriv/slotted), # 2 x 100 mm # 2 x 100 mm 2.5 x 80 mm 0.4 x 2.5 x 80 mm 0.8 x 4 x 100 mm 1 x 5.5 x 125 mm meter for slotted screws, 0.6 x 3.5 x 100 mm
1x 1x 1x 1x 1x 1x 1x 1x 1x 1x 1x 1x	PZ 1 x 80 mm PZ 2 x 100 mm rs (Pozidriv/slotted), # 2 x 100 mm # 2 x 100 mm 2.5 x 80 mm 0.4 x 2.5 x 80 mm 0.8 x 4 x 100 mm 1 x 5.5 x 125 mm neter for slotted screws, 0.6 x 3.5 x 100 mm
1x rew 1x 1x 1x 1x 1x 1x 1x 1x	PZ 2 x 100 mm rs (Pozidriv/slotted), # 2 x 100 mm # 2 x 100 mm 2.5 x 80 mm 0.4 x 2.5 x 80 mm 0.8 x 4 x 100 mm 1 x 5.5 x 125 mm neter for slotted screws, 0.6 x 3.5 x 100 mr
rew 1x 1x 1x 1x 1x 1x 1x 1x	rs (Pozidriv/slotted), # 2 x 100 mm # 2 x 100 mm 2.5 x 80 mm 0.4 x 2.5 x 80 mm 0.8 x 4 x 100 mm 1 x 5.5 x 125 mm neter for slotted screws, 0.6 x 3.5 x 100 mm
1x 4 x 2 1x 1x 1x 1x	# 2 x 100 mm 2.5 x 80 mm 0.4 x 2.5 x 80 mm 0.8 x 4 x 100 mm 1 x 5.5 x 125 mm meter for slotted screws, 0.6 x 3.5 x 100 mm
1x 4 x 2 1x 1x 1x 1x	# 2 x 100 mm 2.5 x 80 mm 0.4 x 2.5 x 80 mm 0.8 x 4 x 100 mm 1 x 5.5 x 125 mm meter for slotted screws, 0.6 x 3.5 x 100 mm
1x 1x 1x dian	0.4 x 2.5 x 80 mm 0.8 x 4 x 100 mm 1 x 5.5 x 125 mm neter for slotted screws, 0.6 x 3.5 x 100 mm
1x 1x 1x dian	0.4 x 2.5 x 80 mm 0.8 x 4 x 100 mm 1 x 5.5 x 125 mm neter for slotted screws, 0.6 x 3.5 x 100 mm
1x 1x 1x dian	0.4 x 2.5 x 80 mm 0.8 x 4 x 100 mm 1 x 5.5 x 125 mm neter for slotted screws, 0.6 x 3.5 x 100 mm
1x dian	1 x 5.5 x 125 mm neter for slotted screws, 0.6 x 3.5 x 100 mm
1x dian	1 x 5.5 x 125 mm neter for slotted screws, 0.6 x 3.5 x 100 mm
(10	x 80 mm
1x	TX 10 x 80 mm
1x	TX 15 x 80 mm
1x	TX 20 x 80 mm
1x	TX 25 x 100 mm
1x	TX 30 x 100 mm
1	4.5-6 x 41 mm
IX	4.3-0 X 41 IIIIII
1x	6.0-8.5 x 41 mm
30	x 392 mm
	344 x 30 x 392 mm
in the	previous model 05501051001 of the roller cabinet.
	1x (30 1x

Web link https://products.wera.de/en/roller_cabinet_and_foam_inserts_foam_inserts_for_roller_cabinet_9711.html

Wera - 9711 05150102001 - 4013288225320

Foam inserts for roller cabinet

