Stanley Discoverer STJM158

\sim				
(, \cap \)	m	$n \sim c$	nitio.	n
\sim	1111	DU	sitio	

94% recycled polyester 6% elastane

Printing guide

Screen print	• 0 0	Waterbase / Plastisol Need special inks for low curing temperature. Anti-migration layer is reccomended.	
Discharge	000	Not applicable	
Transfer -DTF, Flock, Flex, Screen Transfer,	•••	Follow transfer supplier instructions. Use type of glue adequate for max 130°C. Anti-migration layer is reccomended. Steam after press to limit shiny marks.	
Direct To Garment 000		Not applicable	
Embroidery	•••	Direct embroidery, stitched patch, loop labels	
Sublimation	000	Not applicable	