Stella Discoverer STJW159

_			٠.	
(:\	m	$n \cap$	SIT	ion
\sim		\sim	\circ	

94% recycled polyester 6% elastane

Printing guide

Screen print	• 0 0	Waterbase / Plastisol Need special inks for low curing temperature. Anti-migration layer is reccomended.	
Discharge	000	Not applicable	
Transfer -DTF, Flock, Flex, Screen Transfer,	•••	Follow transfer supplier instructions. Use type of glue adequate for max 130°C. Anti-migration layer is reccomended. Steam after press to limit shiny marks.	
Direct To Garment 000 Not applicable		Not applicable	
Embroidery •••		Direct embroidery, stitched patch, loop labels	
Sublimation	000	Not applicable	